



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 256RTI2 2-1/2" Raintight Diecast Compression Connector

*Nsi Industries*

Catalog Number	256RTI2
Manufacturer	Nsi Industries
Description	2-1/2" Raintight Insulated Connector, NPT Thread
Weight per unit	1.2 (lbs/each)
Product Category	Liquid Tight Fittings

### Features

Connector Type	Compression
insulation	Insulated Throat
media	Yes

### Dimensions and Weight

Size	2-1/2
------	-------

### Descriptions

Description	2-1/2" RAIN TIGHT DIECAST COMPRESSION CONNECTOR
extra long description	BPT 256-RTI2 2-1/2" RAIN TIGHT INS
Features	Think Orange: Quality In, Water Out. Listed for Damp or Wet Locations.
Long Description	2-1/2" Raintight Insulated Connector, NPT THREAD
Product Type	2-1/2" Rain Tight Ins Conn
Special Features	The Dual Internal sealing rings create a raintight seal.

### Manufacturer Information

Brand	Bridgeport
GTIN	00781747192561
Manufacturers Part Number	256-RTI2
UPC	781747192561

### Taxonomies, Classifications, and Categories

Category Description	METALLIC FITTINGS
Type	Raintight Compression

### Trade Size

Trade Size	2-1/2
------------	-------

### Packaging

Carton	12
Weight Per each	1.1916



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Compression style connector with internal sealing ring and knockout gasket to create a raintight seal when connecting EMT to box or enclosure. With Bridgeport's newly redesigned Raintight Compression Connectors, 256-RTI2 thru 259-RTI2, contractors can install just one wet location fitting for either thread less Rigid / IMC or EMT. These 2-1/2" dual Listed Zinc Alloy fittings come standard with a 105° C temperature rated insulated throat and the words "Rigid / EMT and RAIN TIGHT" clearly cast into the body.

standard

cULus