



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



257SRTI 3" Ins Steel Emt Raintight Compression Conn *Bridgeport Fittings*

Catalog Number	257SRTI
Manufacturer	Bridgeport Fittings
Description	Connector, Compression, Steel, Insulated Throat - 105 Degree C, Size 3"
Weight per unit	2.2 (lbs/each)
Product Category	Steel Insulated Straight Compr

Features

Connector Type	Steel Raintight/Concrete-Tight Insulated
insulation	Insulated Throat
Material	Steel
media	Yes

Material, Color, and Finish

Finish	Zinc Electroplated
--------	--------------------

Dimensions and Weight

Size	3
------	---

Descriptions

Description	3" INS STEEL EMT RAINLIGHT COMPRESSION CONN
extra long description	BPT 257-SRTI 3" STEEL RAINLIGHT CON
Features	Think Orange: Quality In, Water Out. Listed for Damp or Wet Locations.
Long Description	Connector, Compression, Steel, Insulated Throat - 105 Degree C, size 3"
Product Type	3" Steel Raintight Conn, Ins
Special Features	Connectors assembled with knockout gasket, no separate pieces to buy and stock

Manufacturer Information

Brand	Bridgeport
GTIN	00781747122575
Manufacturers Part Number	257-SRTI
UPC	781747122575

Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	3
------------	---



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	2
Package	10
Weight Per each	2.1663

Uses, Certifications, and Standards

Application	Used to join EMT to box or enclosure. Concrete/Raintight. Insulated Throat - 105°C. Patented
standard	cULus
Temperature Rating	105°C