



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



25T1024PK120V 25W 120V T10 Med Base Clear Incand Lamp

Ge By Current Lamps

Catalog Number	25T1024PK120V
Manufacturer	Ge By Current Lamps
Description	Ge, 25T10 24PK, 25 WTT, 120 V, 250 LM, 1.25 In Diameter, 5.62 In Length, Medium Screw (E26) Base, 1000 HR Average Life
Weight per unit	0.1000 (lbs/each)
Product Category	Incandescent Tubular T Shape L

Features

average life	1000.0
Base	Medium Screw (E26)
lumens	250.0
Voltage Rating	120.0
Wattage	25.0

Material, Color, and Finish

Color	Clear
Finish	Clear

Dimensions and Weight

Diameter	1.25
Length	5.62

Descriptions

Description	25W 120V T10 MED BASE CLEAR INCAND LAMP
extra long description	GEL 25T10-24PK-120 14880 INCANDES
Long Description	GE, 25T10 24PK, 25 WTT, 120 V, 250 LM, 1.25 IN Diameter, 5.62 IN Length, Medium Screw (E26) Base, 1000 HR Average Life
Product Type	14880 Incandescent Lamps

Manufacturer Information

Brand	GE Current
GTIN	00043168148801
Manufacturers Part Number	25T10-24PK-120
UPC	043168148801

Taxonomies, Classifications, and Categories

Category Description	INCANDESCENT
----------------------	--------------

Packaging

Carton	1
Package	24
Weight Per each	0.1

Uses, Certifications, and Standards

Application	STANDARD
-------------	----------