

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301460095](#)
Status: **Active**
Overview: [Watertite® Wet-Location Wiring Solutions](#)
Description: Watertite Connector with Locking Blade, 2 Pole/3 Wire, NEMA L7-15, 277V, Cord Grip Body Size F2

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
UL E10176

General

Product Family Wiring Devices
Series [130146](#)
IP Rating IP67
NEMA Configuration NEMA L7-15
Overview [Watertite® Wet-Location Wiring Solutions](#)
Product Literature Order No 987650-8067
Product Name Watertite
Receptacle Type Single
Specialty N/A
Type Connector
UPC 78678871304
Woodhead Yes

Physical

Cord Grip Body Size F2 1/2"
Flange No
Flip Lid No
Gender Female
Length N/A
Locking Blade Yes
Poles 2-pole/3-wire

Electrical

Cord Type N/A
Current - Maximum per Contact 15.0A
GFCI No
Lighted Connector No
Voltage - Maximum 277V

Material Info

Engineering Number 25W34



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130146](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301460095](#)
Status: **Active**
Overview: [Watertite® Wet-Location Wiring Solutions](#)
Description: Watertite Connector with Locking Blade, 2 Pole/3 Wire, NEMA L7-15, 277V, Cord Grip Body Size F2

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
UL E10176

General

Product Family Wiring Devices
Series [130146](#)
IP Rating IP67
NEMA Configuration NEMA L7-15
Overview [Watertite® Wet-Location Wiring Solutions](#)
Product Literature Order No 987650-8067
Product Name Watertite
Receptacle Type Single
Specialty N/A
Type Connector
UPC 78678871304
Woodhead Yes

Physical

Cord Grip Body Size F2 1/2"
Flange No
Flip Lid No
Gender Female
Length N/A
Locking Blade Yes
Poles 2-pole/3-wire

Electrical

Cord Type N/A
Current - Maximum per Contact 15.0A
GFCI No
Lighted Connector No
Voltage - Maximum 277V

Material Info

Engineering Number 25W34



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130146](#) Series