



M18™ Cordless LITHIUM-ION 2-Tool Combo Kit



2691-22



What's Included


- (1) M18™ Compact 1/2" Drill Driver (Bare Tool) (2606-20)
- (1) M18™ 1/4" Hex Impact Driver (Bare Tool) (2656-20)
- (2) M18™ Compact REDLITHIUM™ Battery (48-11-1815)
- (1) M18™ & M12™ Multi-Voltage Charger (48-59-1812)
- (1) Contractor Bag

Where to Buy

-  Shop Online
-  Find Local

Overview

The 2691-22 M18™ Cordless 2-Tool Combo Kit includes the M18™ Compact Driver (2606-20) and the M18™ 1/4" Hex Impact Driver (2656-20). The M18™ Cordless LITHIUM-ION System's patented technologies and electronics, innovative motor design, and superior ergonomics provide the most efficient blend of power, weight and performance in the industry. Powered by RED LITHIUM™, the M18 cordless LITHIUM-ION system delivers more torque, more power, and longer run-time than the competition.



Features

- Milwaukee® 4-Pole Frameless Motor: Features a robust design combined with rare-earth magnets for longer life, best-in-class 500 in-lbs of torque and 0-400/0-1,800 RPM
- Compact Design: Allows greater accessibility in tight work spaces.
- All-Metal Gear Case and Chuck: Provide maximum impact and shock durability
- REDLINK™ Intelligence: Advanced overload protects the tool against abusive situations and provides maximum life

Specifications

Voltage	18V
Length	7-1/4"
Weight	2.9 lbs
LED Light	Yes
Peak Torque	500 in-lbs
Chuck Type	1/2" Metal Single Sleeve - Ratcheting Lock
Speed	0-400/ 0-1,800 RPM

Tool Warranty	5 Years
----------------------	---------



M18™ 1/4" Hex Impact Driver (Bare Tool)
 Cat. # 2656-20

Features

- Milwaukee® 4-Pole Frameless Motor: Features a robust design for longer life, more power and more runtime than any brushed competitor
- Milwaukee® designed Impact Mechanism: Delivers maximum power and application speed for greater efficiency on the job
- REDLINK™ Intelligence: Provides optimized performance and overload protection using total system communication between tool, battery and charger
- 1/4" Hex Quick-Connect Chuck

Specifications

Voltage	18V
Length	5-1/2"
Weight	3.1 lbs
No Load RPM	0-2,750
On Board FUEL Gauge	Fuel Gauge on Battery
LED Light	Yes
Anvil Size and Type	1/4" Hex Quick Change
No Load IPM	0-3,450
Torque	1,500 in-lbs
Package Type	Tool-Only (No Battery or Charger Included)
Tool Warranty	5 Years



M18™ Cordless LITHIUM-ION 2-Tool Combo Kit



2691-22



What's Included

- (1) M18™ Compact 1/2" Drill Driver (Bare Tool) (2606-20)
- (1) M18™ 1/4" Hex Impact Driver (Bare Tool) (2656-20)
- (2) M18™ Compact REDLITHIUM™ Battery (48-11-1815)
- (1) M18™ & M12™ Multi-Voltage Charger (48-59-1812)
- (1) Contractor Bag

Where to Buy

-  Shop Online
-  Find Local

Overview

The 2691-22 M18™ Cordless 2-Tool Combo Kit includes the M18™ Compact Driver (2606-20) and the M18™ 1/4" Hex Impact Driver (2656-20). The M18™ Cordless LITHIUM-ION System's patented technologies and electronics, innovative motor design, and superior ergonomics provide the most efficient blend of power, weight and performance in the industry. Powered by RED LITHIUM™, the M18 cordless LITHIUM-ION system delivers more torque, more power, and longer run-time than the competition.



Features

- Milwaukee® 4-Pole Frameless Motor: Features a robust design combined with rare-earth magnets for longer life, best-in-class 500 in-lbs of torque and 0-400/0-1,800 RPM
- Compact Design: Allows greater accessibility in tight work spaces.
- All-Metal Gear Case and Chuck: Provide maximum impact and shock durability
- REDLINK™ Intelligence: Advanced overload protects the tool against abusive situations and provides maximum life

Specifications

Voltage	18V
Length	7-1/4"
Weight	2.9 lbs
LED Light	Yes
Peak Torque	500 in-lbs
Chuck Type	1/2" Metal Single Sleeve - Ratcheting Lock
Speed	0-400/ 0-1,800 RPM

Tool Warranty	5 Years
----------------------	---------



M18™ 1/4" Hex Impact Driver (Bare Tool)
 Cat. # 2656-20

Features

- Milwaukee® 4-Pole Frameless Motor: Features a robust design for longer life, more power and more runtime than any brushed competitor
- Milwaukee® designed Impact Mechanism: Delivers maximum power and application speed for greater efficiency on the job
- REDLINK™ Intelligence: Provides optimized performance and overload protection using total system communication between tool, battery and charger
- 1/4" Hex Quick-Connect Chuck

Specifications

Voltage	18V
Length	5-1/2"
Weight	3.1 lbs
No Load RPM	0-2,750
On Board FUEL Gauge	Fuel Gauge on Battery
LED Light	Yes
Anvil Size and Type	1/4" Hex Quick Change
No Load IPM	0-3,450
Torque	1,500 in-lbs
Package Type	Tool-Only (No Battery or Charger Included)
Tool Warranty	5 Years