
26W75 WATERTIGHT NEMA 4X/6P LOCKING PLUG, YELLOW

26W75 | [Pass & Seymour](#)



FEATURES & BENEFITS

Locking Watertight Plug, 20amp 3 ϕ 250 volt, NEMA Configuration L15-20, multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P & IP67 rated.

- Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather.
- Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.
- Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.
- Devices resist high-pressure hose down of 1,500 psi.
- Color coded sealing bushings provided for large range of cord diameters
- Large ribs on body for a superior grip when mating.

SPECIFICATIONS

GENERAL INFO

Color: Yellow

Type: Plug

Features: Watertight

Number Of Poles: 3

Number Of Wires: 4

Special Features: Watertight, NEMA

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 42M

CSA Standard: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121403

DIMENSIONS

Diameter (US): 2.29"

Length (US): 3.10"

TECHNICAL INFORMATION

Amps: 20A
Material: Rubber
NEMA Configuration Number: L15-20
NEMA Rating: 4X/6P
Volts: 3°, 250
Volts (AC): 3°, 250

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant



26W75 WATERTIGHT NEMA 4X/6P LOCKING PLUG, YELLOW

26W75 | [Pass & Seymour](#)



FEATURES & BENEFITS

Locking Watertight Plug, 20amp 3[∅] 250 volt, NEMA Configuration L15-20, multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P & IP67 rated.

- Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather.
- Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.
- Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.
- Devices resist high-pressure hose down of 1,500 psi.
- Color coded sealing bushings provided for large range of cord diameters
- Large ribs on body for a superior grip when mating.

SPECIFICATIONS

GENERAL INFO

Color: Yellow

Type: Plug

Features: Watertight

Number Of Poles: 3

Number Of Wires: 4

Special Features: Watertight, NEMA

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 42M

CSA Standard: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121403

DIMENSIONS

Diameter (US): 2.29"

Length (US): 3.10"

TECHNICAL INFORMATION

Amps: 20A
Material: Rubber
NEMA Configuration Number: L15-20
NEMA Rating: 4X/6P
Volts: 3°, 250
Volts (AC): 3°, 250

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

