



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2711 Turnlok Plug 4W 30A 125/250V B&W *Leviton Manufacturing*

Catalog Number	2711
Manufacturer	Leviton Manufacturing
Description	30 Amp, 125/250 Volt, Nema L14-30P, 3P, 4W, Locking Plug, Industrial Grade, Grounding - Black-White
Weight per unit	0.4000 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	30
connection	Screwed Terminal
Cord Type	S;SO;SOO;ST;STO;STOO;STOW-A;STW;STW-A
horsepower	2 (L-N);2 (L-L)
Material	Impact Modified Nylon
Number of Wires	4
Phase	3
Poles	3
Voltage Rating	125;250
Wire Size	18-10

Dimensions and Weight

Length	2.7
--------	-----

Descriptions

Description	TURNLOK PLUG 4W 30A 125/250V B&W
extra long description	LEV 2711 EB PLUG LOCK 3P4W L14-30P
Long Description	30 Amp, 125/250 Volt, NEMA L14-30P, 3P, 4W, Locking Plug, Industrial Grade, Grounding - Black-White
Product Type	Eb Plug Lock 3P4W L14-30P 30A125/250V

Manufacturer Information

Brand	Leviton
GTIN	00078477808351
Manufacturers Part Number	2711
UPC	078477808351

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	LOCKING PLUG

Packaging

Carton	1
Weight Per each	0.4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Industrial
environmental conditions	Flammability (Rated V-2 per UL 94); Operating Temperature Range (-40 to +60 DEG C)
Mounting	Cable
nema rating	L14-30P
standard	ANSI (C-73); CSA Certified (File LR-406); NEMA (WD-1, WD-6); NOM Certified (057); UL Fed Spec WC-596 (File E13393); UL498 (File E13393)