

Eaton 275B-BOX

Catalog Number: 275B-BOX

Eaton commercial grade combination switch, Stand, #14 - #12 AWG, 15A, Commer, 120/277V, bk and sd wiring, togg, Maint closure, Screw, Brass, Brown, -20-60°C, (1) 1-pole, (1) 3-way, dplx, thermoplas

General specifications

Product Name	Catalog Number
Eaton commercial grade combination switch	275B-BOX
	UPC
	032664161100
Product Length/Depth	Product Height
4.25 in	1.88 in
Product Width	Product Weight
1.75 in	0.2 lb
Compliances	Certifications
RoHS Compliant	cULus Listed
	NOM



Product specifications

Connector type

Screw

Switch type

Single-pole, three-way

Configuration

(2) toggle

Closure type

Maintained

Color

Brown

Wiring method

Back and side

Material

Thermoplastic

Mounting method

Flush

Allowable wire size

#14-12 AWG

Amperage Rating

15A

Number Of Poles

Single-pole

Contact type

Brass

Type

Standard

Device grade

Commercial

Style type

Duplex

Operating temperature

-20 to 60 °C

Number of ways

Three-way

Resources

Catalogs

[Arrow Hart Buyers Guide Section E](#)

Specifications and datasheets

[Eaton Specification Sheet - 275B-BOX](#)

Voltage rating

120/277 V

Application

Commercial

Torque rating

12-14 lbf-inch

Actuator

Toggle



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)