

# Eaton 276W-BOX

Catalog Number: 276W-BOX

Eaton commercial grade combination switch, Stand, #14 - #12 AWG, 15A, Commer, 120/277V, bk and sd wiring, togg, Maint closure, Screw, Brass, wht, -20-60°C, (2) 3-way, dplx, thermoplas



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton commercial grade combination switch	276W-BOX
	UPC
	032664161605
<b>Product Length/Depth</b>	<b>Product Height</b>
4.25 in	1.88 in
<b>Product Width</b>	<b>Product Weight</b>
1.75 in	0.2 lb
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	cULus Listed
	NOM

## Product specifications

### Connector type

Screw

### Switch type

(2) Three-way

### Configuration

(2) toggle

### Closure type

Maintained

### Color

White

### Wiring method

Back and side

### Material

Thermoplastic

### Mounting method

Flush

### Allowable wire size

#14-12 AWG

### Amperage Rating

15A

### Contact type

Brass

### Type

Standard

### Device grade

Commercial

### Style type

Duplex

### Operating temperature

-20 to 60 °C

### Number of ways

(2) Three-way

### Voltage rating

120/277 V

### Application

## Resources

### Catalogs

[Arrow Hart Buyers Guide Section E](#)

### Specifications and datasheets

[Eaton Specification Sheet - 276W-BOX](#)

Commercial

Torque rating

14 lbf-inch

Actuator

Toggle



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)