

## Medium Base Lampholder

276WH



Medium base, phenolic, one-piece keyless, 4 terminals with tri-drive screws, fits 3 1/4" and 4" boxes, with cage neck. White.

### features & benefits

- Quality Materials.
- Durability.
- Time-tested design.

### specifications

**General Info**

Type: Incandescent Medium Base Lampholder

**Listing Agencies/Third Party Information**

CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPS C: 39111803  
UR: No

**Dimensions**

Diameter U S: 4.5"

**Technical Information**

Volts: 250V  
Volts A C: 250  
Watts: 660

**Buy American Act Compliance**

Country of Origin: CHINA  
Buy American Act Status: No