

Eaton 277W-BOX

Catalog Number: 277W-BOX

Eaton commercial grade combination switch, Neon pil lgt, Stand, #14 - #12 AWG, 15A, Commer, 120V (Switch), 125V (pil lgt), bk and sd wiring, togg, Maint closure, Screw, Brass, wht, -20-60°C, 1-pole, dplx, thermoplas, 1 / 25W



General specifications

Product Name	Catalog Number
Eaton commercial grade combination switch	277W-BOX
	UPC
	032664750335
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
1.08 in	0.2 lb
Compliances	Certifications
RoHS Compliant	cULus Listed

Product specifications

Connector type

Screw

Switch type

Single-pole

Configuration

Toggle switch

125V pilot light

Closure type

Maintained

Color

White

Wiring method

Back and side

Wattage

1/25 W

Material

Thermoplastic

Mounting method

Flush

Allowable wire size

#14-12 AWG

Amperage Rating

15A

Number Of Poles

Single-pole

Contact type

Brass

Type

Standard

Device grade

Commercial

Style type

Duplex

Illumination

Neon pilot

Resources

Catalogs

[Arrow Hart Buyers Guide E-18](#)

Specifications and datasheets

[Eaton Specification Sheet - 277W-BOX](#)

Operating temperature

-20 to 60 °C

Voltage rating

120V (Switch)

125V (Pilot Light)

Application

Commercial

Torque rating

12-14 lbf-inch

Actuator

Toggle



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)