

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3520 S Sam Houston Pkwy East Suite 900 77047-0000, TX Houston Phone: 281-412-7049

Fax: 281-412-7314



27W48 Turnlok Conn IP67 20A 250V L620R

Pass & Seymour/Legrand

| Catalog Number | 27W48 |
|------------------|--|
| Manufacturer | Pass & Seymour/Legrand |
| Description | Locking Watertight Connector, 20 Amp 250 Volt, Nema |
| | Configuration L6-20, Multipoint Sealing System Provides |
| | Environmental Protection Of Nema 4, 4X, 6, 6P, and IP67 Rated. |
| Weight per unit | 0.8300 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| tures | |
|------------------|---|
| amperage rating | 20 |
| Cord Type | 12/3 SJ, 14/3 S to 10/3 S, .475" min to .720" max |
| indoor/outdoor | Both |
| Material | Rubber |
| Number of Phases | 1.0 |
| Number of Wires | 3.0 |
| Phase | Single |
| Poles | 2 |
| Voltage | 250.0 V |
| Voltage Rating | 125 |
| Wire Size | 14 - 10 AWG |

Material, Color, and Finish

| Color | Yellow |
|-------|--------|
| COIOI | TEHOW |

Descriptions

| Description | TURNLOK CONN IP67 20A 250V L620R |
|------------------------|--|
| extra long description | P&S 27W48 TURNLOK CONN IP67 20A 250 |
| Features | Watertight |
| Long Description | Locking Watertight Connector, 20 amp 250 volt, NEMA Configuration L6-20, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated. |
| Product Type | Turnlok Conn IP67 20A 250V L620R |
| Special Features | Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation. |



ELLIOTT ELECTRIC SUPPLY 3520 S Sam Houston Pkwy East Suite 900 77047-0000, TX Houston Phone: 281-412-7049 Phone: 281-412-7049

We Deliver...Lower Cost, Quality Products, & Personal Service

Fax: 281-412-7314

| Manufacturer I | nformation |
|----------------|------------|
|----------------|------------|

| Brand | LEGRAND-PASS & SEYMOUR |
|---------------------------|------------------------|
| GTIN | 00785007033779 |
| Manufacturers Part Number | 27W48 |
| UPC | 785007033779 |

Taxonomies, Classifications, and Categories

| Category Description | Residential receptacles |
|----------------------|-------------------------|
| Туре | CONNECTOR |

Trade Size

| Amperage | 20.0 |
|----------|------|
| Amperage | 20.0 |

Packaging

| ckagnig | | |
|-----------------|----|--|
| Carton | 1 | |
| Package | 10 | |
| Weight Per each | | |

Uses, Certifications, and Standards

| and Standards | |
|--------------------------|---|
| Application | High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors Thermoplastic elastomer body resists water, oils, lubricants and soaps while |
| | maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings Ideal for washdown areas — rated wa |
| environmental conditions | Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized |
| nema rating | L6-20R |
| standard | UL Listed, CSA Listed |
| | |