



**SNA Terminal Blocks**  
**T&B Catalog Number:**

029006917  
 66201997016  
 Active

**UPC Number:**  
**Status:**  
**Description:**

Green and yellow ground block with 6 mm spacing on a DIN 3 rail and spring clamp connection

**Features**

- Top entry wire connection
- Touch-safe IP20 protection

**Application**

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

**General**

Style	Ground Block
Color	Green and Yellow
Mounting	DIN 3
Series	D 4/6.P.2L
Connection Technology	Spring Clamp
UL Wire Range (AWG)	24-10
Rated IEC Wire Range (Solid) (mm <sup>2</sup> )	0.2 - 6
Rated IEC Wire Range (Stranded) (mm <sup>2</sup> )	0.2 - 4

**Dimension Information**

L x W x H (mm)	62.5 x 6 x 38
Spacing (mm)	6
L x W x H (in)	2.46 x .238 x 1.49
Spacing (inches)	.238

**Specifications**

Rated UL Wire Size (AWG)	10
--------------------------	----

**Packaging**

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	750
T&B Sold in UOM	Each
T&B Weight Per UOM	0.03 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com



**SNA Terminal Blocks**  
**T&B Catalog Number:**

029006917  
 66201997016  
 Active

**UPC Number:**  
**Status:**  
**Description:**

Green and yellow ground block with 6 mm spacing on a DIN 3 rail and spring clamp connection

**Features**

- Top entry wire connection
- Touch-safe IP20 protection

**Application**

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

**General**

Style	Ground Block
Color	Green and Yellow
Mounting	DIN 3
Series	D 4/6.P.2L
Connection Technology	Spring Clamp
UL Wire Range (AWG)	24-10
Rated IEC Wire Range (Solid) (mm <sup>2</sup> )	0.2 - 6
Rated IEC Wire Range (Stranded) (mm <sup>2</sup> )	0.2 - 4

**Dimension Information**

L x W x H (mm)	62.5 x 6 x 38
Spacing (mm)	6
L x W x H (in)	2.46 x .238 x 1.49
Spacing (inches)	.238

**Specifications**

Rated UL Wire Size (AWG)	10
--------------------------	----

**Packaging**

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	750
T&B Sold in UOM	Each
T&B Weight Per UOM	0.03 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com