



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2905 Rac 1-1/4" Emt Compression Conn

Hubbell--Raco

| | |
|------------------|---|
| Catalog Number | 2905 |
| Manufacturer | Hubbell--Raco |
| Description | Compression Connector, Uninsulated, Steel, 1-1/4 In. Trade Size |
| Weight per unit | 0.3990 (lbs/each) |
| Product Category | Steel Uninsulated Straight Com |

Features

| | |
|-------------------|-------------|
| Conduit Type | EMT |
| fitting type | Connectors |
| installation type | Screw |
| Insulation Type | UNINSULATED |
| pallet quantity | 2500 |

Material, Color, and Finish

| | |
|-------|--------|
| Color | Silver |
|-------|--------|

Dimensions and Weight

| | |
|--------|-----|
| Length | 2.1 |
|--------|-----|

Descriptions

| | |
|------------------------|--|
| Description | RAC 1-1/4" EMT COMPRESSION CONN |
| extra long description | RACO 2905 EMT COMPR CONNECTOR 1-1/4 |
| Long Description | COMPRESSION CONNECTOR, UNINSULATED, STEEL, 1-1/4 IN. TRADE SIZE |
| Product Type | Commercial Fittings |
| Special Features | Zinc electro plated |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | RACO |
| GTIN | 00050169029053 |
| Manufacturers Part Number | 2905 |
| UPC | 050169029053 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | STEEL EMT FITTINGS |
| Type | Compression connector, uninsulated, EMT |

Trade Size

| | |
|------------|----------|
| Trade Size | 1-1/4 in |
|------------|----------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 0.399 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|------------------|
| Application | Electrical |
| standard | UL 514B |