



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 29W77 Turnlok Conn IP67 4W 30A 600V L1730R

*Pass & Seymour/Legrand*

|                  |  |
|------------------|--|
| Catalog Number   | 29W77  |
| Manufacturer     | Pass & Seymour/Legrand   |
| Description      | Locking Watertight Connector, 30AMP 3Y 600VOLT, Nema Configuration L17-30, Multipoint Sealing System Provides Environmental Protection Of Nema 4, 4X, 6, 6P, and IP67 Rated. |
| Weight per unit  | 0.8300 (lbs/each)  |
| Product Category | Plugs, Connectors, Inlets, Out   |

### Features

|                 |   |
|-----------------|---|
| amperage rating | 30  |
| Cord Type       | 12/4 S to 8/4 S, 6/4 MSHA, .640" min to .930" max |
| Material        | Rubber  |
| Number of Wires | 4.0   |
| Phase           | Single  |
| Poles           | 3-way   |
| Voltage Rating  | 600   |
| Wire Size       | 12 - 6 AWG  |

### Material, Color, and Finish

|       |        |
|-------|--------|
| Color | Yellow |
|-------|--------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | TURNLOK CONN IP67 4W 30A 600V L1730R   |
| extra long description | P&S 29W77 TL CONN IP67 4W 30A 600V   |
| Long Description       | Locking Watertight Connector, 30amp 3Y 600volt, NEMA Configuration L17-30, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated.   |
| Product Type           | TL Conn IP67 4W 30A 600V L1730R  |
| Special Features       | Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation. |

### Manufacturer Information

|                           |                        |
|---------------------------|------------------------|
| Brand                     | LEGRAND-PASS & SEYMOUR |
| GTIN                      | 00785007033731         |
| Manufacturers Part Number | 29W77                  |
| UPC                       | 785007033731           |

### Taxonomies, Classifications, and Categories

|                      |                         |
|----------------------|-------------------------|
| Category Description | Residential receptacles |
| Type                 | Locking Connector       |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Amperage ..... 30.0

## Packaging

Carton ..... 1

Package ..... 10

Weight Per each ..... 0.83

## Uses, Certifications, and Standards

Application

High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors | Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings | Ideal for washdown areas — rated wa

environmental conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized

nema rating

L17-30R

standard

UL Listed, CSA Listed