

Project		Catalog #		Type	
Prepared by		Notes		Date	



Metalux

APVT

4' Vaportite Industrial LED

Typical Applications

• Industrial • Manufacturing • Gymnasium • Warehouse

Interactive Menu

- Order Information page 2
- Photometric Data page 2
- Energy Data page 2
- Product Warranty


Product Certification



Top Product Features

- Durable gray polycarbonate housing with integrated metal gear tray
- High Impact Polycarbonate optical lens
- Available in 4ft, with lumen packages up to 6,000 lumens
- Wet Location listed
- High-Performance efficacy up to 123 lm/W

Dimensional and Mounting Details



Order Information by Catalog Number

Catalog Number	Description	UPC	Delivered Lumens	Watts	Efficacy (lm/W)
4APVTLD-54L835	4ft, Vaportite, LED, 5400 lumen, UNV, Fixed Output, 3500K, Wet Location	080083801343	6090	50	121
4APVTLD-54L840	4ft, Vaportite, LED, 5400 lumen, UNV, Fixed Output, 4000K, Wet Location	080083802166	6209	50	123

Product Specifications

Construction

- High-impact gray polycarbonate housing with interated metal gear tray
- Standard housings available with one 7/8" conduit entry point
- Durable cam latches clamp diffuser tightly for a positive seal between housing and diffuser
- Electrical components and fixtures are UL/cUL listed for wet location, IP65 rated

Electrical

- Long-Life LED system coupled with a fixed output driver to deliver optimal performance
- LED's available in 3500, 4000 and 5000K with a CRI ≥ 80
- Projected life is L70 at 54,000 hours
- cULus listed
- Electronic drivers are available for 120-277V applications

Warranty

- Vaportite LED features a five year limited warranty

Compliance


- UL/cUL listed for Wet location
- RoHS compliant, and LED modules comply with IESNA LM-79 and LM-80 standards

Lens

- Thermoformed low profile, highimpact frosted lens with general distribution

Photometric Data

[View IES files](#)



4APVTLD-40L840

Electronic Driver
 Linear LED 4000K
 Spacing criterion: (H) 1.2 x mounting height,
 (L) 1.3 x mounting height
 Lumens: 5115
 Input Watts: 39W
 Efficacy: 131 lm/W
 Test Report: 4APVTLD-40L840.IES

Energy and Performance Data

Lumen Maintenance

Ambient Temperature	TM-21 Lumen Maintenance (54,000 hours)
25°C	> 70%

Input Watts

4APVTLD-54=50W

Shipping Data

Catalog No.	Wt.
4APVTLED	10 lbs.

Project		Catalog #		Type	
Prepared by		Notes		Date	



Metalux

APVT

4' Vaportite Industrial LED

Typical Applications

• Industrial • Manufacturing • Gymnasium • Warehouse

Interactive Menu

- Order Information page 2
- Photometric Data page 2
- Energy Data page 2
- Product Warranty


Product Certification



Top Product Features

- Durable gray polycarbonate housing with integrated metal gear tray
- High Impact Polycarbonate optical lens
- Available in 4ft, with lumen packages up to 6,000 lumens
- Wet Location listed
- High-Performance efficacy up to 123 lm/W

Dimensional and Mounting Details



Order Information by Catalog Number

Catalog Number	Description	UPC	Delivered Lumens	Watts	Efficacy (lm/W)
4APVTLD-54L835	4ft, Vaportite, LED, 5400 lumen, UNV, Fixed Output, 3500K, Wet Location	080083801343	6090	50	121
4APVTLD-54L840	4ft, Vaportite, LED, 5400 lumen, UNV, Fixed Output, 4000K, Wet Location	080083802166	6209	50	123

Product Specifications

Construction

- High-impact gray polycarbonate housing with interated metal gear tray
- Standard housings available with one 7/8" conduit entry point
- Durable cam latches clamp diffuser tightly for a positive seal between housing and diffuser
- Electrical components and fixtures are UL/cUL listed for wet location, IP65 rated

Electrical

- Long-Life LED system coupled with a fixed output driver to deliver optimal performance
- LED's available in 3500, 4000 and 5000K with a CRI ≥ 80
- Projected life is L70 at 54,000 hours
- cULus listed
- Electronic drivers are available for 120-277V applications

Warranty

- Vaportite LED features a five year limited warranty

Compliance


- UL/cUL listed for Wet location
- RoHS compliant, and LED modules comply with IESNA LM-79 and LM-80 standards

Lens

- Thermoformed low profile, highimpact frosted lens with general distribution

Photometric Data

[View IES files](#)



4APVTLD-40L840

Electronic Driver
 Linear LED 4000K
 Spacing criterion: (H) 1.2 x mounting height,
 (L) 1.3 x mounting height
 Lumens: 5115
 Input Watts: 39W
 Efficacy: 131 lm/W
 Test Report: 4APVTLD-40L840.IES

Energy and Performance Data

Lumen Maintenance

Ambient Temperature	TM-21 Lumen Maintenance (54,000 hours)
25°C	> 70%

Input Watts

4APVTLD-54=50W

Shipping Data

Catalog No.	Wt.
4APVTLED	10 lbs.