




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2RB14X 16-14 Vinyl Ins Butt Splice

Abb Installation Products, Inc

| | |
|------------------|--|
| Catalog Number | 2RB14X |
| Manufacturer | Abb Installation Products, Inc |
| Description | Expanded Vinyl-Insulated Butt Splice, Length 1.13 Inches, Width .26 Inches, Maximum Insulation Diameter .200, Wire Range #16-#14 Awg, Color Blue, Copper, Tin Plated |
| Weight per unit | 0.0050 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|--------|
| Material | Copper |
| Voltage Rating | 600 V |

Material, Color, and Finish

| | |
|--------|---------------------|
| Color | Blue |
| Finish | Electro -Tin Plated |

Descriptions

| | |
|------------------------|--|
| Description | 16-14 VINYL INS BUTT SPLICE |
| extra long description | ABB 2RB14X EXP INS VINYL BUTT SPLCE |
| Long Description | Expanded Vinyl-Insulated Butt Splice, Length 1.13 Inches, Width .26 Inches, Maximum Insulation Diameter .200, Wire Range #16-#14 AWG, Color Blue, Copper, Tin Plated |
| Product Type | Exp Ins Vinyl Butt Splice, 16-14 Le |
| Special Features | In butt splices, the wires are butted together and crimped at each end of the splice. These splices are color-coded according to wire size |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Sta-Kon |
| GTIN | 00786210807201 |
| Manufacturers Part Number | 2RB14X |
| UPC | 786210807201 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | TERMINALS |
| Type | Vinyl Insulated Butt Splice |

Packaging

| | |
|-----------------|-------|
| Carton | 100 |
| Weight Per each | 0.005 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard UL E9809

Temperature Rating 105 C