



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2RC10X 12-10 Vinyl Ins Butt Splice

Abb Installation Products, Inc

Catalog Number	2RC10X
Manufacturer	Abb Installation Products, Inc
Description	Expanded Vinyl-Insulated Butt Splice, Length 1.31 Inches, Width .31 Inches, Maximum Insulation Diameter .250, Wire Range #12-#10 Awg, Color Yellow, Copper, Tin Plated, Mini-Pack
Weight per unit	0.0100 (lbs/each)
Product Category	Small Terminals & Connectors

Features

Material	Copper
Voltage Rating	600 V

Material, Color, and Finish

Color	Yellow
Finish	Electro -Tin Plated

Descriptions

Description	12-10 VINYL INS BUTT SPLICE
extra long description	ABB 2RC10X EXP INS VINYL BUTT SPLCE
Long Description	Expanded Vinyl-Insulated Butt Splice, Length 1.31 Inches, Width .31 Inches, Maximum Insulation Diameter .250, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated, Mini-Pack
Product Type	Exp Ins Vinyl Butt Splice, 12-10 Le
Special Features	In butt splices, the wires are butted together and crimped at each end of the splice. These splices are color-coded according to wire size

Manufacturer Information

Brand	Sta-Kon
GTIN	00786210807218
Manufacturers Part Number	2RC10X
UPC	786210807218

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Vinyl Insulated Butt Splice

Packaging

Carton	50
Package	250
Weight Per each	0.01



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard	UL E9809 / UL E9809
Temperature Rating	105 C