



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



30076 Wiretwist Wire Connector, WT6 Red, 100/Box

Ideal

Catalog Number	30076
Manufacturer	Ideal
Description	Ideal, Wire Connector, Wire-Nut, Twist-On, Number Of Conductors: 1 to 6, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Conductor Range: 18 - 12 Awg, Min 2-18 Max 4-14 W/ 1-18, Material: Flame-Retardant Polypropelene, Color: Red, Voltage Rating: 600 V, Model Number: 76B, Flammability Rating: UI 94V-2
Weight per unit	0.9100 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Flame-retardant Polypropelene
Voltage Rating	600

Material, Color, and Finish

Color	Red
-------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	WIRETWIST WIRE CONNECTOR, WT6 RED, 100/BOX
extra long description	IDEAL 30-076 WIRENUT 76B RED, 100 B
Features	The IDEAL Wire-Nut Wire Connector set new standards for innovation, quality and convenience when it was first introduced in 1928. As the first screw-on wire connector in America, it literally set the industry standard for years to come. With a fixed, square-wire spring and a positive grip shell, the Wire-Nut is perfect to twist-on with fingers for a secure connection that will last. The refined wire range makes it the best choice for fine stranded wire applications. The Wire-Nut also features a tough, flame
Long Description	IDEAL, Wire Connector, Wire-Nut, Twist-On, Number Of Conductors: 1 to 6, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Conductor Range: 18 - 12 AWG, Min 2-18 MAX 4-14 w/ 1-18, Material: Flame-retardant polypropelene, Color: Red, Voltage Rating: 600 V, Model Number: 76B, Flammability Rating: UL 94V-2
Product Type	Wirenut 76B Red, 100 BX
Special Features	Comply With Federal Specification W-S-610E;Deep Skirt Helps Protect Against Flash-Over;Features: Fixed, Square-Wire Spring Creates Its Own Threads Maintains A Secure Positive Grip That Will Not Relax Over Time;Flammability Rating: UL 94V-2;Model Number: 76B;No Pre-Twisting Required Positive Grip Design Provides Fast, Easy Installation;Reusable For Easy Circuit Changes And Additions;Tough, UL94V-2 Flame-Retardant Shell Rated At 105 Degree C (221 Degree F);UL Listed To 486C And CSA Certified To C22.2 #188

Manufacturer Information

Brand	Ideal
GTIN	00783250300761
Manufacturers Part Number	30-076
UPC	783250300761

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	Twist-On

Packaging

Carton	100
Package	1000
Weight Per each	0.91



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Insulating or Joining 2 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA Certified to C22.2 #188, UL Listed to 486C, complies with Federal Specification W-S-610E