



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 30090J In-Sure Push-In Wire Conn, 90 8-PRT BLCK, 100/Jar *Ideal*

Catalog Number	30090J
Manufacturer	Ideal
Description	Ideal 30-090J Push-In 12AWG 8-Port,
Weight per unit	1.5 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### Features

connection	8 Ports
Voltage Rating	600 V Maximum Building Wire, 1000 V Maximum Signs And Lighting Fixtures
Wire Size	#12 AWG - #20 AWG Solid, #14 AWG - #16 AWG (19 Strand Or Less) #18 AWG (7 Strand Or Less) Stranded, #12 AWG - #14 AWG (19 Strand Or Less) #16 AWG (26 Strand Or Less) 318 AWG (16 Strand Or Less) Stranded (Tin Bonded)
Wire Type	Solid, Stranded, Stranded (Tin Bonded)

### Material, Color, and Finish

Color	Black
-------	-------

### Dimensions and Weight

Size	0.355 IN Length X 1.380 IN Width X 0.717 IN Height
------	--

### Descriptions

Description	IN-SURE PUSH-IN WIRE CONN, 90 8-PRT BLCK, 100/JAR
Features	The In-Sure Push-In Wire Connector is perfect for residential, light commercial, lighting retrofit, and pre-fab wiring systems, or any other branch circuit wiring application where a traditional twist-on wire connector would be used. Simply push the wire in – the low insertion force makes it easy. The color-coded shell allows for quick identification of port configuration while the clear polycarbonate housing allows for visual verification of every connection. The ergonomic design is easier to grip which me
Long Description	IDEAL 30-090J PUSH-IN 12AWG 8-PORT,
Product Type	Push-In 12AWG 8-Port, 100 Jar
Special Features	Features: No-Twist Connection Reduces Repetitive Motion Fatigue; Low Insertion Force For Fast And Easy Connections; Compact Size Makes Installation Easy; Clear Shell Gives Visual Verification Of Connection; UL Listed To 486C And CSA Certified To C22.2 #188; UL 467 Listed For Grounding And Bonding Applications; 600V Maximum Building Wire, 1000V; Maximum Signs And Lighting Fixtures; Shell Rated To 105 DEG C; Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 DEG F); Model: 90



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Ideal
GTIN	00783250460878
Manufacturers Part Number	30-090J
UPC	783250460878

## Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Push-In

## Availability

Manufacturer Status	Inactive
minimum qty	100

## Packaging

Carton	100
Package	600
Weight Per each	1.46

## Uses, Certifications, and Standards

Application	For Grounding And Bonding Applications
standard	CSA C22.2 #188, 486C/467 UL Listed, RoHS
Temperature Rating	105 DEG C Shell Rated