



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 301039J In-Sure Push-In Wire Conn, 39 3-Port Blue, 150/Jar

*Ideal*

Catalog Number	301039J
Manufacturer	Ideal
Description	Ideal, Wire Connector, In-Sure, Push-In, Size: 0.780 In Length X 0.86 In Width X 0.450 In Height, Connection: 3 Ports, Wire Size: #10 Awg - #14 Awg Solid, #10 Awg - #12 Awg (19 Strand or Less) Stranded, #10 Awg - #14 Awg (19 Strand or Less) Stranded (Tin Bonded), Color: Blue, Voltage Rating: 600 V Maximum Building Wire, 1000 V Maximum Signs and Lighting Fixtures, Temperature Rating: 105 Deg C Shell Rated, Wire Type: Solid, Stranded, Stranded (Tin Bonded), Model: 39
Weight per unit	0.0093 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### Features

connection	3 Ports
Voltage Rating	600 V Maximum Building Wire, 1000 V Maximum Signs And Lighting Fixtures
Wire Size	#10 AWG - #14 AWG Solid, #10 AWG - #12 AWG (19 Strand Or Less) Stranded, #10 AWG - #14 AWG (19 Strand Or Less) Stranded (Tin Bonded)
Wire Type	Solid, Stranded, Stranded (Tin Bonded)

### Material, Color, and Finish

Color	Blue
-------	------

### Dimensions and Weight

Size	0.780 IN Length X 0.86 IN Width X 0.450 IN Height
------	---



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	IN-SURE PUSH-IN WIRE CONN, 39 3-PORT BLUE, 150/JAR
extra long description	IDEAL 30-1039J PUSH-IN 10AWG 3-PORT
Features	Ergonomic design for easy grip and comfortable installationLow insertion force for fast and easy connectionsCompact size makes installation easyClear shell gives visual verification of connectionTough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)Approved for bonding and grounding applicationsStrip, push, connect – the fastest way to make a connection.The In-Sure Push-In Wire Connector is perfect for residential, light commercial, lighting retrofit, and pre-fab wiring systems, or any other branch c
Long Description	IDEAL, Wire Connector, In-Sure, Push-In, Size: 0.780 IN Length X 0.86 IN Width X 0.450 IN Height, Connection: 3 Ports, Wire Size: #10 AWG - #14 AWG Solid, #10 AWG - #12 AWG (19 Strand Or Less) Stranded, #10 AWG - #14 AWG (19 Strand Or Less) Stranded (Tin Bonded), Color: Blue, Voltage Rating: 600 V Maximum Building Wire, 1000 V Maximum Signs And Lighting Fixtures, Temperature Rating: 105 DEG C Shell Rated, Wire Type: Solid, Stranded, Stranded (Tin Bonded), Model: 39
Product Type	Push-In 10AWG 3-Port, 150 Jar
Special Features	Features: No-Twist Connection Reduces Repetitive Motion Fatigue; Low Insertion Force For Fast And Easy Connections; Compact Size Makes Installation Easy; Clear Shell Gives Visual Verification Of Connection; UL Listed To 486C And CSA Certified To C22.2 #188; UL 467 Listed For Grounding And Bonding Applications; 600V Maximum Building Wire, 1000V; Maximum Signs And Lighting Fixtures; Shell Rated To 105 DEG C; Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 DEG F); Model: 39

## Manufacturer Information

Brand	Ideal
GTIN	00783250693658
Manufacturers Part Number	30-1039J
UPC	783250693658

## Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	Push-In

## Availability

minimum qty	150
-------------	-----



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	150
Package	900
Weight Per each	0.0093

## Uses, Certifications, and Standards

Application	For Grounding And Bonding Applications
standard	CSA C22.2 #188, 486C/467 UL Listed, RoHS
Temperature Rating	105 DEG C Shell Rated