



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



301160 Underground Wire Conn, 60 Gray/Gray, 25/Card

Ideal

Catalog Number	301160
Manufacturer	Ideal
Description	MDL 60 Gray Gray Ug 25 Clam
Weight per unit	0.0160 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

Quantity	Box of 25
----------	-----------

Material, Color, and Finish

Color	Gray
-------	------

Descriptions

Description	UNDERGROUND WIRE CONN, 60 GRAY/GRAY, 25/CARD
extra long description	IDEAL 30-1160 MDL 60 GRAY GRAY UG 2
Features	100% Silicone-based sealant protects against moisture and corrosionUL Listed to 486G Sealed Twist-On Wire Connector for use in damp/wet locations or above-grade applicationsEasy to apply, pre-filled twist-on wire connectorsExpanding, live-action square-wire spring for fast, secure and long-lasting connectionsDeep skirt provides superior moisture resistance to protect connectionsTough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)For use in damp/wet location or direct burial/below-grade applications
Long Description	MDL 60 GRAY GRAY UG 25 CLAM
Product Type	MDL 60 Gray Gray Ug 25 Clam
Special Features	Smallest wet location/direct burial connector with widest wire range. Non-hardening sealant completely seals out moisture to protect fungus and corrosion. Sealant is stable down to -40° C. Flame-retardant Shell

Manufacturer Information

Brand	Ideal
GTIN	00783250758197
Manufacturers Part Number	30-1160
UPC	783250758197

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Model 60® Wire Connector



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty 25

Packaging

Carton 25

Package 125

Weight Per each 0.016

Uses, Certifications, and Standards

Application Handles wire sizes from #20 to #10 AWG copper. Minimum of 1
#20 with 1 #18. Maximum of 2 #12 & 1 #10 AWG.

standard UL Listed and CSA Certified