



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2509 West 5th
79072-0000, TX Plainview
Phone: 806-296-5518
Fax: 806-291-0839

303410 Sol Wire GRND Tail -Loop/GRD SCRW-Stripped, 50/Bag

Ideal

Catalog Number	303410
Manufacturer	Ideal
Description	Grounding Tail, Connection: Loop With Ground Screw and Stripped End, Wire Size: 12 Awg, Green, Wire Type: Solid, 10 In Length, Package: 50/Bag, C/Us UI Listed, Ensures Compliance With Nec Standards, Rohs Compliant, For Device Grounding Applications
Weight per unit	0.0250 (lbs/each)
Product Category	Splicing & Terminating Kits

Descriptions

Description	SOL WIRE GRND TAIL -LOOP/GRD SCRW-STRIPPED, 50/BAG
extra long description	IDEAL 30-3410 12 AWG,10" SOLID W GR
Features	Coming in various lengths and styles, IDEAL Grounding Pigtailes are designed for a wide variety of grounding applications to help ensure compliance with Article 250 of the National Electric Code. Whether you need solid or stranded, fork or stripped end, small packaging for the occasional use or bulk packaging for the big jobs, we have a solution. The ultra-flexible lead wire and bonding jumpers make for fast and efficient pigtail and the thread-forming, hole finding ground screw cuts down on installation
Long Description	Grounding Tail, Connection: Loop With Ground Screw And Stripped End, Wire Size: 12 AWG, Green, Wire Type: Solid, 10 IN Length, Package: 50/Bag, C/US UL Listed, Ensures Compliance With NEC Standards, RoHS Compliant, For Device Grounding Applications
Product Type	12 Awg, 10" Solid W GRND Screw

Manufacturer Information

Brand	Ideal
GTIN	00783250679508
Manufacturers Part Number	30-3410
UPC	783250679508

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
----------------------	--------------------------

Availability

minimum qty	50
-------------	----

Packaging

Carton	50
Weight Per each	0.025