

Vertical Self-Closing Covers with lock hasps

- Heavy duty die-cast aluminum, .094" thick with powder finish.
- Stainless steel springs, screws, and shaft.
- Durable heavy-duty gasket.
- Meets all Federal specifications.
- Lock hasp diameter ¼".
- Specials available upon request (for 1-gang special, please use item #30560).
- UL Listed.
- All covers on this page are made in the USA. The plug-in receptable that is supplied with our 30513 cover, however, is not.



Catalog No.	Opening/Description	Mounting	Carton Quantity	Weight per 100 units
30522 30522W 30522Z	All duplex receptacles and combination devices (Also available in white & bronze)	Standard	25	48 lbs.
30523	All duplex receptacles and combination devices	4-screw (FS)	25	48 lbs.
30525	Standard single receptacles (1.405" diam.)	Standard	25	48 lbs.
30526	Standard single receptacles (1.405" diam.)	4-screw (FS)	25	48 lbs.
30528	20A and 30A TL receptacles (1.625" diam.)	Standard	25	48 lbs.
30529	20A and 30A TL receptacles (1.625" diam.)	4-screw (FS)	25	48 lbs.
30531	30A 3- and 4-wire TL receptacles (1.75" diam.)	Standard	25	48 lbs.
30532	30A 3- and 4-wire TL receptacles (1.75" diam.)	4-screw (FS)	25	48 lbs.
30534	30A and 50A range/dryer receptacles (2.125" diam.)	Standard	25	48 lbs.
30535	30A and 50A range/dryer receptacles (2.125" diam.)	4-screw (FS)	25	48 lbs.
30537 30537W 30537Z	GFI receptacles (Also available in white & bronze)	Standard	25	48 lbs.
30538	GFI receptacles	4-screw (FS)	25	48 lbs.

Motor Base Receptacle and Self-closing cover for mobile homes

Catalog No.	Opening/Description	Carton Quantity	Weight per 100 units
30513	Horizontal self-closing cover No. 30507 with 2-screw mounting. Comes with receptacle rated at 15A-125V; with male device 30-wire U ground parallel blades.	100	45 lbs.