



## 30826 1800W 120V Photo Cell

*Mulberry Metal*

|                  |  |
|------------------|--|
| Catalog Number   | 30826  |
| Manufacturer     | Mulberry Metal   |
| Description      | Mulberry; Photo Control; Direct Wire-In; Supply Voltage: 120 V; Timing Range: 15 S; Connection: 1/2-14 In Threaded Stem; Mounting: Fixed or Swivel; Enclosure: High Impact Polycarbonate; Operating Temperature: -40 to 158 Deg F; Tungsten Watts: 1800 WTT; Tungsten Amps: 15 Amp; Ballast Watts: 1000 WTT; Ballast Amps: 8.3 Amp |
| Weight per unit  | 0.3800 (lbs/each)  |
| Product Category | Lighting Photocells  |

### Features

|                |                         |
|----------------|-------------------------|
| connection     | 1/2-14 IN Threaded Stem |
| supply voltage | 120                     |
| Timing Range   | 15                      |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 1800W 120V PHOTO CELL  |
| extra long description | MULB 30826 120V SWIVEL PHOTO CONTROL   |
| Long Description       | Mulberry; Photo Control; Direct Wire-In; Supply Voltage: 120 V; Timing Range: 15 S; Connection: 1/2-14 IN Threaded Stem; Mounting: Fixed Or Swivel; Enclosure: High Impact Polycarbonate; Operating Temperature: -40 To 158 DEG F; Tungsten Watts: 1800 WTT; Tungsten Amps: 15 AMP; Ballast Watts: 1000 WTT; Ballast Amps: 8.3 AMP |
| Product Type           | 120V Swivel Photo Control  |

|                  |  |
|------------------|--|
| Special Features | Features: High Impact Polycarbonate Housing; Turn On Between 1 And 5 Foot Candles; Turn On/Turn Off Ratio 1 To 3; Single-Pole, Single-Throw Switching; Minimum Time Delay 15 Seconds; Contact Position At Night Normally Closed; External Slide Clip Allows Light Level Adjustment; With 2 IN - 14 Threaded Stem Fits 2 IN Knockout; With 6 IN Color-Coded Lead Wire; Temperature Range -40 Deg F (-40 Deg C) To 158 Deg F (70 Deg C); Tungsten Watts: 1800 WTT; Tungsten Amps: 15 AMP; Ballast Watts: 1000 WTT; Ballast Amps: |
|------------------|--|

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Mulberry       |
| GTIN                      | 00095327308267 |
| Manufacturers Part Number | 30826          |
| UPC                       | 095327308267   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2450 NE Inner Loop Building 1  
78626-0000, TX Georgetown  
Phone: 737-444-2615  
Fax: 737-444-2617

## Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | Commercial dimmers, motion sensors, & photo cells |
| Type                 | Direct Wire-In                                    |

## Availability

|        |          |
|--------|----------|
| Status | Inactive |
|--------|----------|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 10   |
| Weight Per each | 0.38 |

## Uses, Certifications, and Standards

|                       |                           |
|-----------------------|---------------------------|
| Application           | For Wet Locations         |
| Enclosure             | High Impact Polycarbonate |
| Mounting              | Fixed Or Swivel           |
| Operating Temperature | -40 to 158                |
| standard              | UL Listed, CSA Certified  |