



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



3232BK 15A/125V Duplex Recp Side + Speed

Pass & Seymour/Legrand

Catalog Number	3232BK
Manufacturer	Pass & Seymour/Legrand
Description	Straight Blade Receptacle, 15 A, 125 V, 2 Poles, 3 Wires, #14 to #12 Awg Compatible Wire Size, Grounding Connection, Wall Mount, 1.32 In Length, 0.960 In Width, 3.31 In Height, Thermoplastic, Black, Impact Resistant, 0.1300 LB
Weight per unit	0.1283 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Grounding
indoor/outdoor	Indoor
Outlet Type	Commercial, Indoor, Residential
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wire Size	14 - 12

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	4.2 in
------	--------

Descriptions

Description	15A/125V DUPLEX RECP SIDE + SPEED
extra long description	P&S 3232BK 15A/125V RECEPT DUPLEX S

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007419399
Manufacturers Part Number	3232BK
UPC	785007419399

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Outlet

Trade Size

Amperage	15.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Package	200
Weight Per each	0.1283

Uses, Certifications, and Standards

Mounting	WALL
standard	UL, CULUS, UL 498