



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



3232TRBK TR Duplex Recp 15A/125V BK

Pass & Seymour/Legrand

Catalog Number	3232TRBK
Manufacturer	Pass & Seymour/Legrand
Description	Straight Blade Duplex Receptacle, 15 A, 125 V, 2 Poles, 3 Wires, #14 to #12 Awg Compatible Wire Size, Grounding Connection, Wall Mount, 1.320 In Length, 1.0 In Width, 3.31 In Height, Thermoplastic, Black, Tamper Resistant, Impact Resistant, 0.1300 LB
Weight per unit	0.1329 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

indoor/outdoor	Indoor
media	Yes
Outlet Type	Residential, Indoor, Tamper-Resistant, Commercial
Poles	Double Pole
Voltage	125.0 V
Wire Size	14 - 12 AWG

Material, Color, and Finish

Finish	Matte
--------	-------

Descriptions

Description	TR DUPLEX RECP 15A/125V BK
extra long description	P&S 3232TRBK TR DUP REC 15A/125V BK

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007240306
UPC	785007240306

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Outlet

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	10
Package	200
Weight Per each	0.1329

Uses, Certifications, and Standards

standard	UL, cULus
----------	-----------