

TradeMaster Tamper- Resistant Receptacle

3232TRBK

Tamper-Resistant Duplex Grounding
Receptacle. 15 amp, 125 volt. Black.



features & benefits

- Meets 2008 National Electrical Code Tamper-Resistant requirements.
- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- High-impact resistant thermoplastic construction.
- Extra-long strap.
- Quickloop wire looping aid.
- Long-term blade retention.
- Longer tri-drive screws for easier 12 AWG looping.
- Extra-large circuit break-off tabs.
- Side-access push wire release.
- Ultrasonic welding of face to back body.
- Side wire accepts #12 – #14 AWG solid wire.
- Push wire accepts #14 AWG solid only.
- Superior protection than traditional outlet caps or protection plates.
- Low profile face.
- Traditional contoured face (3232 models).
- Self-grounding models provide automatic ground clip.

specifications

General Info

Color: Black
Type: Tamper-Resistant

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No.42
CSA Standard: Yes
cULus: Yes
Federal Spec: No
UL Listing No: UL498
UL Standard: Yes
UN SPS C: 39121406

Dimensions

Depth U S: 1"
Height U S: 3.31"
Width U S: 1.32"

Technical Information

Amps: 15 Amp
Volts A C: 125

Buy American Act Compliance

Country of Origin: CHINA
Buy American Act Status: No

TradeMaster Tamper- Resistant Receptacle

3232TRBK

Tamper-Resistant Duplex Grounding
Receptacle. 15 amp, 125 volt. Black.



features & benefits

- Meets 2008 National Electrical Code Tamper-Resistant requirements.
- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- High-impact resistant thermoplastic construction.
- Extra-long strap.
- Quickloop wire looping aid.
- Long-term blade retention.
- Longer tri-drive screws for easier 12 AWG looping.
- Extra-large circuit break-off tabs.
- Side-access push wire release.
- Ultrasonic welding of face to back body.
- Side wire accepts #12 – #14 AWG solid wire.
- Push wire accepts #14 AWG solid only.
- Superior protection than traditional outlet caps or protection plates.
- Low profile face.
- Traditional contoured face (3232 models).
- Self-grounding models provide automatic ground clip.

specifications

General Info

Color: Black
Type: Tamper-Resistant

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No.42
CSA Standard: Yes
cULus: Yes
Federal Spec: No
UL Listing No: UL498
UL Standard: Yes
UN SPS C: 39121406

Dimensions

Depth U S: 1"
Height U S: 3.31"
Width U S: 1.32"

Technical Information

Amps: 15 Amp
Volts A C: 125

Buy American Act Compliance

Country of Origin: CHINA
Buy American Act Status: No