

fiberglassBOX™ Three Gang

Residential Switch or Receptacle Box



3300-NC3



3300-NK



3303-NK



3300-NBC3



3300-NBK



3303-NBK

Nail-On	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	46.0	3300-N	Angled mid-nails, Speed Klamps™ - bulk packed	3	5-11/16	3-3/4	14175	20	15
	46.0	3300-NC3	Angled mid-nails, 3 wire clamps - factory installed	3	5-11/16	3-3/4	14190	20	16
	46.0	3300-NC6	Angled mid-nails, 6 wire clamps - factory installed	3	5-11/16	3-3/4	14205	20	18
	46.0	3300-NK	Angled mid-nails, Speed Klamps™ - factory installed	3	5-11/16	3-3/4	14177	20	16
	56.5	3303-N	Angled mid-nails, Speed Klamps™ - bulk packed	3-9/16	5-11/16	3-3/4	15200	20	18
	56.5	3303-NC6	Angled mid-nails, 6 wire clamps - factory installed	3-9/16	5-11/16	3-3/4	15211	20	19
	56.5	3303-NK	Angled mid-nails, Speed Klamps™ - factory installed	3-9/16	5-11/16	3-3/4	15201	20	18

Nail-On with Bar	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	46.0	3300-NB	Angled mid-nails, adjustable stabilizing bar, Speed Klamps™ - bulk packed	3	5-11/16	3-3/4	14210	20	21
	46.0	3300-NBC3	Angled mid-nails, adjustable stabilizing bar, 3 wire clamps - factory installed	3	5-11/16	3-3/4	14225	20	22
	46.0	3300-NBK	Angled mid-nails, adjustable stabilizing bar, Speed Klamps™ - factory installed	3	5-11/16	3-3/4	14212	20	21
	56.5	3303-NB	Angled mid-nails, adjustable stabilizing bar, Speed Klamps™ - bulk packed	3-9/16	5-11/16	3-3/4	15207	20	23
	56.5	3303-NBK	Angled mid-nails, adjustable stabilizing bar, Speed Klamps™ - factory installed	3-9/16	5-11/16	3-3/4	15208	20	23



3300-SSK



3303-SSK



3300-SSBK

Steel Stud Screws	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	46.0	3300-SS	Steel stud screws for use with non-load-bearing studs 22 gauge or lighter, Speed Klamps™ - bulk packed	3	5-11/16	3-3/4	14522	20	16
	46.0	3300-SSK	Steel stud screws for use with non-load-bearing studs 22 gauge or lighter, Speed Klamps™ - factory installed	3	5-11/16	3-3/4	14524	20	16
	56.5	3303-SS	Steel stud screws for use with non-load-bearing studs 22 gauge or lighter, Speed Klamps™ - bulk packed	3-9/16	5-11/16	3-3/4	15203	20	17
	56.5	3303-SSK	Steel stud screws for use with non-load-bearing studs 22 gauge or lighter, Speed Klamps™ - factory installed	3-9/16	5-11/16	3-3/4	15204	20	17

Steel Stud Screws with Bar	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	46.0	3300-SSB	Steel stud screws for use with non-load-bearing studs 22 gauge or lighter, adjustable stabilizing bar, Speed Klamps™ - bulk packed	3	5-11/16	3-3/4	14521	20	21
	46.0	3300-SSBK	Steel stud screws for use with non-load-bearing studs 22 gauge or lighter, adjustable stabilizing bar, Speed Klamps™ - factory installed	3	5-11/16	3-3/4	14523	20	22

All dimensions are in inches unless otherwise noted.
See page 7 for Attachment Coding suffix descriptions.

Competitive Cross Reference

Fiberglass Outlet Boxes



ALLIED
MOULDED
PRODUCTS, Inc.

fiberglassBOX™: Premium Series “Hard Box” Fiberglass Boxes

Allied Moulded	Carlton® PH (Union Phenolic)	Carlton® PC Black Polycarbonate	Carlton® PVC (Zip Blue)	Carlton® PVC (SuperBlue®)	Cantex® (EZ BOX®)	Pass & Seymour (Slater®)
1096-N	1040/2000/1240	118-N	B118A	N/A	EZ18SN	P118R
1096-NR	N/A	N/A	N1-710-M	N/A	N/A	P118RN
1096-SS	N/A	N/A	N/A	N/A	EZ18SNZ	S118RS
1096-Z2	N/A	118-LB	N/A	N/A	N/A	S118S25
1096-Z4	2000-738	118-LB	B118B	N/A	N/A	S118S50
1098-N	1250/1050	120-N	B120A	N/A	EZ20SN/EZ20SB	N/A
1098-NR	N/A	N/A	N/A	N/A	N/A	N/A
1098-SS	1250-S	N/A	N/A	N/A	EZ20SNZ	N/A
1098-Z2	N/A	N/A	N/A	N/A	N/A	N/A
1098-Z4	1250-112	N/A	N/A	N/A	N/A	N/A
1098-Z4H	N/A	N/A	N/A	N/A	N/A	PH1-22-B
1099-N	1260	122-N	RN-23	BH122A	EZ23SN	P122R
1099-NR	N/A	N/A	N/A	N/A	N/A	P122RN
1099-NRED	N/A	N/A	N/A	N/A	EZ20SNAR	N/A
1099-SS	1260-S	N/A	RS-23	BH122S	EZ23SNZ	S122RS
1099-Z4	N/A	N/A	N/A	N/A	EZ20SB	S122S50/P122C
2300-Z22	N/A	234-LB	SB2-236-FS	N/A	N/A	S235S50AC
2300-Z22K	N/A	234-LB	SB2-236-FS	N/A	N/A	S235S50AC
2300-N	1052	234-N	B232A/SN234/SN236	BH235A	EZ32DN	S235RAC
2300-NK	1052	234-N	B232A/SN234	BH235A	EZ32DN	S235RAC
2300-SS	1052CS	N/A	N/A	BH235S	EZ32DNZ	N/A
2300-SSK	1052CS	N/A	N/A	BH235S	EZ32DNZ	N/A
2300-Z2	2002-738	N/A	B232B	N/A	N/A	N/A
2300-Z2K	2002-738	N/A	B232B	N/A	N/A	N/A
2300-Z4	N/A	N/A	N/A	N/A	N/A	N/A
2300-Z4K	N/A	N/A	N/A	N/A	N/A	N/A
2302-N	1072-C	N/A	SN236/SN241	BH235A	EZ48DN	N/A
2302-NK	1072-C	N/A	SN236/SN241	BH235A	EZ48DN	N/A
2302-NKRED	N/A	N/A	N/A	N/A	N/A	N/A
2302-SS	N/A	N/A	SS241	BH235S	EZ48DNZ	5235RACS
2302-SSK	N/A	N/A	SS241	BH235S	EZ48DNZ	5235RACS
2302-Z4	N/A	N/A	N/A	N/A	N/A	N/A
2302-Z4K	N/A	N/A	N/A	N/A	N/A	N/A
3300-Z22	N/A	345-LB	SB2-357-FS	N/A	N/A	S354S50AC
3300-Z22K	N/A	345-LB	SB2-357-FS	N/A	N/A	S354S50AC
3300-Z24	N/A	N/A	N/A	N/A	N/A	N/A
3300-Z24K	N/A	N/A	N/A	N/A	N/A	N/A
3300-N	1043-C	345-N	B344A/SN357	BH353A	EZ44TN	N/A
3300-NB	N/A	N/A	N/A	N/A	N/A	N/A
3300-NBK	N/A	N/A	N/A	N/A	N/A	N/A
3300-NK	1043-C	345-N	B344A/SN357	BH353A	EZ44TN	N/A
3300-SS	N/A	N/A	SS357	BH353S	EZ44TNZ	N/A
3300-SSB	N/A	N/A	N/A	N/A	N/A	N/A
3300-SSBK	N/A	N/A	N/A	N/A	N/A	N/A
3300-SSK	N/A	N/A	SS357	BH353S	EZ44TNZ	N/A
3300-Z2	N/A	N/A	SB357	N/A	N/A	N/A
3300-Z2B	N/A	N/A	N/A	N/A	N/A	N/A
3300-Z2BK	N/A	N/A	N/A	N/A	N/A	N/A
3300-Z2K	N/A	N/A	SB357	N/A	N/A	N/A
3300-Z4	N/A	N/A	N/A	N/A	N/A	N/A