


Non-Metallic Sheathed Cable Fittings

Steel or malleable iron Two-Screw Connectors

Rounded cable grip and smooth bushing protect the cable sheath and wire insulation. Because saddle is threaded, screws do not travel or extend beyond the connector body as it is clamped to the cable. An extra lip on the saddle closes the unused part of the connector opening.

- Threaded saddle means screws don't travel or extend beyond connector body as it's clamped to cable
- Extra lip on saddle closes unused part of connector opening
- Steel or malleable iron construction
- Look for the unique T&B blue color ensuring the highest quality fitting



NON-INSULATED CAT. NO.	INSULATED CAT. NO.	K.O. SIZE	UL LISTED & CSA CERTIFIED		UL LISTED & CSA CERTIFIED SERVICE ENTRANCE CABLES	IN.			INSULATED CABLE OPENING (IN.)	
			SINGLE NM & NMC CABLE	PAIRS OF NM & NMC CABLE		A	B	C	MAX.	MIN.
3302-TB*	3302M-TB	1/2"	(2) #14, (2) #12, (2) #10, (3) #14, (3) #12, (3) #10	(2) #14, (2) #12	(2) #12 thru (2) #4, (3) #12, (3) #10	1	1 1/2	1	.590	.250
3303-TB	3303M	3/4"	(2) #8, (2) #6, (3) #8, (3) #6, (3) #4	(2) #12, (2) #10, (2) #8, (3) #14	(2) #8 thru (2) 1/0, (3) #8, (3) #6, (2) #6 + #8 GND, (2) #1, (2) 1/0, (3) #6 thru (3) #2	1 1/4	1 1/8	1 1/8	.750	.530
3304	3304M	1"	(3) #8, (3) #6, (3) #4	(2) #8, (3) #10	(2) #4 + #6 GND, (2) #3 + #5 GND, (2) #2 + #4 GND (3) #2 thru (3) 2/0, (2) #1 + #3 GND	1 1/2	1 1/8	1 1/4	.990	.690
3305	3305M	1 1/4"	—	(2) #8, (2) #6, (2) #4, (3) #8	(2) 1/0 + #2 GND, (2) 2/0 + #1 GND	1 3/32	2 1/4	1 1/4	1.320	.850
3306	3306M	1 1/2"	(3) #4, (3) #6	—	(3) 3/0, (3) 4/0, (2) 3/0 + 1/0 GND, (2) 4/0 + 2/0 GND	2 1/16	2 5/16	1 1/16	1.530	.930
3307	3307M	2"	Max. 1.98", Min. 1.15"	Max. 1.98", Min. 1.15"	—	2 3/4	3 3/4	1 1/8	—	—
3308†	—	2 1/2"	Max. 2.38", Min. 1.5"	Max. 2.38", Min. 1.5"	—	3 3/4	3 5/16	2 3/16	—	—
3309†	—	3"	Max. 2.88", Min. 1.75"	Max. 2.88", Min. 1.75"	—	3 11/16	4 1/16	2 7/16	1.980	1.150
3310†	—	3 1/2"	Max. 3.38", Min. 2.25"	Max. 3.38", Min. 2.25"	—	4 1/16	5 1/4	2 21/32	—	—
3311†	—	4"	Max. 3.88", Min. 2.5"	Max. 3.88", Min. 2.5"	—	4 7/8	5 11/16	3 3/32	—	—

*UL Listed for use with rubber and thermoplastic flexible cords (both single and multiple cords and two oval cables).

†UL Listed for multiple cords and cables.

CSA File No. 2884

UL File No. E-23013 - 1/2" - 1 1/2"; U.L. File No. E-15170 - 2"

† Not UL Listed or CSA certified.