



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



35083 Twist-A-Nut Conduit Deburring Tool, Slotted Tip

Ideal

Catalog Number	35083
Manufacturer	Ideal
Description	Ideal, Conduit Deburring Tool, Twist-A-Nut, Slotted Tip, Warranty: Lifetime Guarantee
Weight per unit	0.3333 (lbs/each)
Product Category	Tool Kits

Descriptions

Description	TWIST-A-NUT CONDUIT DEBURRING TOOL, SLOTTED TIP
extra long description	IDEAL 35-083 TWIST-A-NUT CONDUIT DE
Features	Deburs inside and outside edges of 1/2 in., 3/4 in. and 1 in. thin wall conduitHooded tip tightens EMT fitting set screws without slippingSquare tip "seats" much more quickly on fitting screws than slotted versionHead removes and is interchangeable with IDEAL 7-in-1 Twist-a-Nut Screwdriver shaft (#35-908)Head can be used at low speed setting in drill or cordless screwdriver
Long Description	IDEAL, Conduit Deburring Tool, Twist-A-Nut, Slotted Tip, Warranty: Lifetime Guarantee
Product Type	Twist-A-Nut Conduit Deburrer
Special Features	Features: Deburs Inside And Outside Edges Of 1/2, 3/4, And 1 IN Thin Wall Conduit; Hooded Tip Tightens Emt Fitting Set Screws Without Slipping; Removable Head Interchangeable With Ideal 7-In-1 Twist -A-Nut Screwdriver Shaft (35-908); Head Can Be Used In Drill Or Cordless Screwdriver; Universal Wire-Nut Wrench In Handle End Eases Installation Of Twist-On Connectors; Lifetime Guarantee (Excludes Blades); Warranty: Lifetime Guarantee

Manufacturer Information

Brand	Ideal
GTIN	00783250350834
Manufacturers Part Number	35083
sub brand	Twist-A-Nut
UPC	783250350834

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	SLOTTED TIP

Packaging

Carton	1
Weight Per each	0.3333