



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



36432 Power-Spade Spade Bit Kit W/Pouch, 4-Piece

Ideal

Catalog Number	36432
Manufacturer	Ideal
Description	Spade Bit Kit, 5/8 In;3/4 In;7/8 In;1 In Bit Size, 1/4 In Shank Diameter, 4 Pieces, 0.7 LB
Weight per unit	0.7000 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Shank Type	Quick Change Hex
------------	------------------

Descriptions

Description	POWER-SPADE SPADE BIT KIT W/POUCH, 4-PIECE
Features	Kit Includes: 5/8 in. 36-415, 3/4 in. 36-417, 7/8 in. 36-419, 1 in. 36-421 Spade Bits and pouchThe Power-Spade Spade Bit offers industry-leading performance over any other style of spade bit on the market. Designed to meet the requirements of professional electricians, the Power-Spade is a giant leap forward in terms of speed, hole quality and ease of use. The patented full cone threaded tip increases drilling speed and reduces vibration while requiring less force to pull the bit through the material.
Special Features	The most innovative and fastest spade bit ever; Full cone threaded tip for fast and effortless drilling; Contoured paddle provides fast chip removal; Unique spur and reamer design also cuts cleaner entry and exit holes with significantly reduced breakout splintering; Require up to 50 PCT less force to achieve even faster cuts than other leading competitors' spade bits; All bits are 6 IN long and feature a 1/4 IN quick-change hex shank; Max operating speed: 1500 RPM

Manufacturer Information

Brand	Ideal
GTIN	00783250718115
sub brand	Power-Spade
UPC	783250718115

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	Spade Bit Kit

Packaging

Carton	1
Weight Per each	0.7



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

RoHS Compliant