



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



3820 Straight Blade Recp 3P 4W 20A 125V

Pass & Seymour/Legrand

Catalog Number	3820
Manufacturer	Pass & Seymour/Legrand
Description	Straight Blade Receptacle 3-Pole 4-Wire 20A 125/250V
Weight per unit	0.2170 (lbs/each)
Product Category	Wall Plates & Covers

Features

amperage rating	20
connection	Non Ground
Number of Wires	4
Poles	3-way
Voltage	125.0 V
Voltage Rating	125/250
Wire Size	4

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	STRAIGHT BLADE RECP 3P 4W 20A 125V
extra long description	P&S 3820 STR BLD REC 3P 4W 20A 125V
Long Description	Straight Blade Receptacle 3-Pole 4-Wire 20A 125/250V
Product Type	STR BLD Rec 3P 4W 20A 125V
Special Features	Arc-resistant plastic, dead front design & double wire contact

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007790108
Manufacturers Part Number	3820
UPC	785007790108

Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	Straight Blade Receptacle

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	10
Package	20
Weight Per each	0.217



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Industrial Spec Grade
Mounting	WALL
nema rating	14-20
standard	UL, UL 498