



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



416DCI2 2" Ins Diecast Squeeze Connector

Bridgeport Fittings

Catalog Number	416DCI2
Manufacturer	Bridgeport Fittings
Description	Connector, Squeeze, Zinc Die Cast, Insulated Throat, Trade Size 2 Inch
Weight per unit	0.5000 (lbs/each)
Product Category	Liquid Tight Fittings

Features

angle	180 Deg
Connector Type	Squeeze, Insulated
Material	Zinc Die Cast
media	Yes

Material, Color, and Finish

Finish	Ball burnish
--------	--------------

Dimensions and Weight

Size	2
------	---

Descriptions

Description	2" INS DIECAST SQUEEZE CONNECTOR
extra long description	BPT 416-DCI2 2" SQUEEZE CONN. INS.
Long Description	Connector, Squeeze, Zinc Die Cast, Insulated Throat, Trade Size 2 Inch
Product Type	2" Squeeze Conn. Ins. Zinc
Special Features	Furnished with Tri-Drive screw

Manufacturer Information

Brand	Bridgeport
GTIN	00781747164162
Manufacturers Part Number	416-DCI2
UPC	781747164162

Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	2
------------	---

Packaging

Carton	10
Weight Per each	0.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Used to connect flexible metal conduit or armored cable to box or enclosure. Insulator rated 105 degree C.
standard	UL
Temperature Rating	105°C