



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

41878 12W Led T8 48" 3K/35/41K/5K/65K DBL/SNGL End 1800L

Sylvania-Ledvance

| | |
|------------------|--|
| Catalog Number | 41878 |
| Manufacturer | Sylvania-Ledvance |
| Description | 4FT Led T8 Ledlescenttm (UI Type B), Frosted Pet Shatter Resistant Glass, 12W, 120 277V, 82 Cri, 1800 Lumens, 3000K/3500K/4100K/5000K/6500K CCT Selectable, 50, 000 HRS Life, Dimmable |
| Weight per unit | 0.4410 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------|------------------|
| Lamp Type | LED BALLAST-FREE |
|-----------|------------------|

Descriptions

| | |
|------------------------|--|
| Description | 12W LED T8 48" 3K/35/41K/5K/65K DBL/SNGL END 1800L |
| extra long description | SYL LED12T8L48FGPDIM8SC12BF/41878 L |
| Long Description | 4ft LED T8 LEDlescentTM (UL Type B), Frosted PET shatter resistant glass, 12W, 120 277V, 82 CRI, 1800 lumens,3000K/3500K/4100K/5000K/6500K CCT Selectable, 50,000 hrs life, Dimmable |
| Product Type | LED12T8L48FGPDIM8SC12BF 25/CS 1/Sku |

Manufacturer Information

| | |
|---------------------------|------------------------------|
| Brand | SYLVANIA |
| GTIN | 00046135418785 |
| Manufacturers Part Number | LED12T8L48FGDIM8SC12BF/41878 |
| UPC | 046135418785 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|

Packaging

| | |
|-----------------|-------|
| Carton | 25 |
| Weight Per each | 0.441 |