


Steel - Rigid/Liquidtight Transition - Raintight

Images



Application

For creating a Liquidtight/Raintight Connection between 2 different Raceways: 2" Rigid Conduit (GRC &&& IMC) and 2" Liquidtight Flexible Metallic Conduit (LFMC). Suitable for use in wet locations. Concrete Tight

Product Information

Material: Malleable Iron

Finish: Zinc Coated

Certifications & Codes:

CSA File Number: cULus

Federal Specification Number: A-A-50553A

NEMA Standard: FB-1

UL File Number: E9391

UL Standard: 514B

UNSPSC: 39131707

[Download Photo Image](#)

[Download Dimensional Image](#)

Dimension A in Inches: 1-1/4

Dimension B in Inches: 15/16

Dimension C in Inches: 3

Catalog ID: 4375-LT

UPC Number: 78174720375

Description: Combination Coupling for transitioning between 2" Liquidtight Flexible Metallic Conduit (LFMC) and 2" Rigid Steel Conduit. NPSM Threads on Hub. Malleable Iron Body with Steel Ferrule

Application: For creating a Liquidtight/Raintight Connection between 2 different Raceways: 2" Rigid Conduit (GRC &&& IMC) and 2" Liquidtight Flexible Metallic Conduit (LFMC). Suitable for use in wet locations. Concrete Tight

Trade Size: 2"

Std Pkg Qty: 10

Unit Qty: 2