



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 4400S 4" STL Set SCR Emt Conn *Appleton/Oz Gedney*

Catalog Number	4400S
Manufacturer	Appleton/Oz Gedney
Description	Features:2 9/16IN Dia X 5 1/16IN Length, 1 In Thread Length, Concretetight, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:4IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated
Weight per unit	2.2 (lbs/each)
Product Category	Steel Uninsulated Straight Set

### Features

connection	Male NPS Thread
Connector Type	SET SCREW
insulation	Not insulated
Material	Steel

### Material, Color, and Finish

Color	Metallic
Finish	Zinc Electro Plated

### Dimensions and Weight

Size	4
------	---

### Descriptions

Description	4" STL SET SCR EMT CONN
extra long description	EGS 4400S 4 IN EMT SSCR CONN
Long Description	Features:2 9/16IN Dia X 5 1/16IN Length, 1 IN Thread Length, Concretetight, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:4IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated
Product Type	4 In Emt SSCR Conn
Special Features	4 IN Trade Size Connector for EMT Conduit, Set Screw Type, Male Hub Threads NPS, Body Length 3.19 IN, Max. Dia. 4.75 IN, Thread Length 1.00 IN, Concretetight when taped, Male Hub Threads - NPS

### Manufacturer Information

Brand	APPOZGCOMM
GTIN	00687855846412
Manufacturers Part Number	4400S
UPC	687855846412



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	EMT Conduit Straight Set Screw Connector

## Trade Size

Trade Size	4
------------	---

## Packaging

Carton	5
Weight Per each	2.24

## Uses, Certifications, and Standards

Application	To ground and secure EMT Raceways to boxes and enclosures
nema rating	FB-1
standard	UL Standard: 514B; UL Listed: E14815, E14895; CSA Standard: C22.2 No. 18.3, cUL Listed: E14895, CSA Certified: 028507; NEMA: FB-1