



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5668 N. Hwy 81
73533-0000, OK Duncan
Phone: 580-252-2582
Fax: 580-252-2738



44101 Wire Marker Booklet, Asst 0-9, 45 Each

Ideal

Catalog Number	44101
Manufacturer	Ideal
Description	Wire Marker Booklet, Plastic-Impregnated Cloth Material, Non-Smear Black Legend Color, 0-9 Legend, Text, -40 °F Operating Temperature, +180 °F Operating Temperature, 1-1/2 In Length, 1/4 In Width, 0.14 LB/Ea
Weight per unit	0.1400 (lbs/each)
Product Category	Markers & Marking Tapes

Features

Number of Pages	10/Booklet
-----------------	------------

Dimensions and Weight

Size	1/4 X 1-1/2 IN Marker
------	-----------------------

Descriptions

Description	WIRE MARKER BOOKLET, ASST 0-9, 45 EACH
extra long description	IDEAL 44-101 Wire Marker Booklet,ld
Features	Convenient pocket-size bookletsPlastic, cloth construction for long-lasting durabilityResist abrasion, moisture, dirt and oilPerforated 1/4 in. x 1-1/2 in. markers can be separated into half-length sizesNon-smear black legendSelf-sticking on wire and cableFor applications above or below groundTemperature Range: -40°F to 180°F (-40°C to 82°C)Adhesion: 45 oz./in. width ultimate

Manufacturer Information

Brand	Ideal
GTIN	00783250441013
UPC	783250441013

Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
----------------------	----------------------------

Packaging

Carton	1
Package	5
Weight Per each	0.14

Uses, Certifications, and Standards

standard	RoHS
Temperature Rating	-40 To 180