

Eaton 4424 GRT NK

Catalog Number: 4424 GRT NK

Eaton B-Line series wiring trough, 4" height, 24" length, 4" width, GRT NK wiring trough, Embossed thru holes, No knockouts, Screw cover, NEMA 3R, Steel, Plated screws, ANSI 61 gray, 16 gauge

General specifications

Product Name	Catalog Number
Eaton B-Line series wiring trough	4424 GRT NK
UPC	Product Length/Depth
782051140712	24 in
Product Height	Product Width
4 in	4 in
Product Weight	Certifications
7.753 lb	CSA Certified UL Listed



Material/finish

Material thickness

16 gauge

Finish color

ANSI 61 gray

Model

Closure type

Plated screws

Mounting method

Embossed thru holes

Special features

Cover is held secure by flange and plated screws

Type

GRT NK wiring trough

Resources

Catalogs

[Wiring trough section of Electrical Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 4424 GRT NK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)