



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



44791 Safety Lockout Hasp, "Do Not Operate", Red, 1/Card

Ideal

Catalog Number	44791
Manufacturer	Ideal
Description	Ideal, Lockout Hasp, Labeled Safety, Lock Material: Anodized Aluminum Alloy, Color: Red, Legend: Do Not Operate, Finish: Vinyl Coated
Weight per unit	0.4000 (lbs/each)
Product Category	Safety Equipment

Material, Color, and Finish

Color	Red
-------	-----

Descriptions

Description	SAFETY LOCKOUT HASP, "DO NOT OPERATE", RED, 1/CARD
extra long description	IDEAL 44-791 Lockout Hasp,Ideal,Lab
Features	Safety Lockout Hasps by IDEAL allow up to six workers to lock out a single energy source! They are rustproofed, plated and vinyl-coated, and feature an anodized aluminum alloy construction for long-term durability. Permanent "Do Not Operate" labels accept pens, pencils and permanent markers.
Long Description	IDEAL, Lockout Hasp, Labeled Safety, Lock Material: Anodized Aluminum Alloy, Color: Red, Legend: DO NOT OPERATE, Finish: Vinyl Coated
Product Type	Lockout Hasp, Ideal, Labeled Sfty, Andz Al Alloy Lock, Red, LGND:
Special Features	Features: Allow Up To Six Workers To Lock Out A Single Energy Source; Rustproofed, Plated And Vinyl Coated; Labeled Hasps Feature Anodized Aluminum Alloy Construction For Long Term Durability; Permanent "Do Not Operate" Labels Accept Pens, Pencils And Permanent Markers; Legend: DO NOT OPERATE; Finish: Vinyl Coated

Manufacturer Information

Brand	Ideal
GTIN	00783250447916
Manufacturers Part Number	44-791
UPC	783250447916

Taxonomies, Classifications, and Categories

Category Description	SAFETY PRODUCTS
Type	Labeled Safety

Packaging

Carton	1
Weight Per each	0.4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

RoHS