

6-INCH INCANDESCENT SLOPE CEILING HOUSING ICAT




H6451C

FEATURES

- Got Nail™ bar hangers
- Pass-N-Thru™ tool-less shortening of bar hangers
- Slide-N-Side™ wire traps
- Quick Connect™ wiring connectors included in junction box
- AIR-TITE™
- Thermally protected
- Die-formed housing and plaster frame
- Socket aiming for ceilings from 2/12 to 12/12 pitch
- Slope indicator provides quick and consistent lamp settings

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

COMPLIANCES: UL/cUL Listed - Wet Location, UL/cUL Listed - Damp Location, UL/cUL Listed 1598 Luminaire, UL/cUL Listed for Feed Through, UL/cUL Listed for Insulation Contact, AIR-TITE™ Certified ASTM E283



ORDERING INFORMATION: ORDER HOUSING AND TRIMS SEPARATELY*


SAMPLE NUMBER: H6451C - 456W

Housing	Trims	Baffles
H6451C —6" Aperture, New Construction, Slope Ceiling, IC AIR-TITE™, 120V Line Voltage	<p>Adjustables</p> <p>1417 Low Voltage Eyeball with Baffle - 30° Tilt, 50W 12V MR16, OD: 7-1/4" [184mm]</p> <p>1417BA—White Trim with White Eyeball and Black Baffle (Low Voltage Transformer Included)</p> <p>1417W—White Trim with White Eyeball and White Baffle (Low Voltage Transformer Included)</p> <p>417 Coilex® Baffle Eyeball - 30° Tilt, 75W R30, 65W BR30, OD: 8" [203mm]</p> <p>417P—White Trim and Eyeball with Black Coilex® Baffle</p> <p>417PB—Polished Brass Trim and Eyeball with Black Coilex® Baffle</p> <p>417W—White Trim and Eyeball with White Coilex® Baffle</p> <p>78 Eyeball - 30° Tilt, 65W BR30, 75W R30, 75W PAR30L, OD: 8" [203mm]</p> <p>78B—Satin Brass Trim with Satin Brass Eyeball</p> <p>78P—White Trim with White Eyeball</p> <p>78PAT—White Trim with White Eyeball - AIR-TITE™ Trim</p> <p>78PB—Polished Brass Trim with Polished Brass Eyeball</p> <p>78SN—Satin Nickel Trim with Satin Nickel Eyeball</p> <p>78TBZ—Tuscan Bronze Trim with Tuscan Bronze Eyeball</p>	<p>Baffles</p> <p>456 Baffle, 456P: 60W BR30, 50W PAR30L, OD: 7-1/4" [184mm]</p> <p>456P—White Trim with Black Baffle</p> <p>456 Baffle, 456W: 50W PAR30L, 65W BR30, and 75W PAR30L with H1999 Socket Extender, OD: 7-1/4" [184mm]</p> <p>456W—White Trim with White Baffle</p> <p>Lenses and Diffusers</p> <p>170 Albalite Lens with Reflector, 60W A19, OD: 8" [203mm]</p> <p>170P—White Trim with Frosted Albalite Glass Lens</p> <p>170PS—White Trim with Frosted Albalite Glass Lens, Wet Location Listed and AIR-TITE™</p> <p>Reflectors</p> <p>455 Specular Reflector, 65W BR30, 75W R30, 75W PAR30L, OD: 7-1/4" [184mm]</p> <p>455H—White Trim with Haze Reflector</p> <p>455SC—White Trim with Clear Specular Reflector</p> <p>455SCG—White Trim with Champagne Gold Reflector</p>

NOTES: Δ Not to be used in direct contact with spray foam insulation. Δ UL/cUL Listed for Wet Location with select trims.

455 Slope Ceiling Specular Reflector


- 455SC White Trim with Clear Specular Reflector
- 455H White Trim with Haze Reflector
- 455CG White Trim with Champagne Gold Reflector



HOUSING / LAMP:
H6451C: 65W BR30, 75W R30, 75W PAR30L
DIMENSIONS: OD: 7-1/4" [184mm]

456 Slope Ceiling Baffle


- 456W White Trim with White Baffle
- 456P White Trim with Black Baffle



HOUSING / LAMP:
H6451C: 456P: 60W BR30, 50W PAR30L
H6451C: 456W: 50W PAR30L, 65W BR30, 75W PAR30L with H1999 Socket Extender
DIMENSIONS: OD: 7-1/4" [184mm]

78 Eyeball 30° Tilt


- 78P White Trim with White Eyeball
- 78PAT White Trim with White Eyeball - AIR-TITE™ Trim
- 78SN Satin Nickel Trim with Satin Nickel Eyeball
- 78TBZ Tuscan Bronze Trim with Tuscan Bronze Eyeball
- 78B Satin Brass Trim with Satin Brass Eyeball
- 78PB Polished Brass Trim with Polished Brass Eyeball



HOUSING / LAMP:
H6451C: 65W BR30, 75W R30, 75W PAR30L
DIMENSIONS: Height: 4-1/8" [105mm]; Aperture: 3-15/16" [100mm]; OD: 8" [203mm]

170 Albalite Glass Lens with Reflector

- 170P White Trim with Frosted Albalite Glass Lens
- 170PS White Trim with Frosted Albalite Glass Lens, Wet Location, AIR-TITE™



HOUSING / LAMP:
H6451C: 60W A19
DIMENSIONS: Height: 4" [101mm]; OD: 8" [203mm]

417 Coilex® Baffle Eyeball 30° Tilt


- 417W White Trim and Eyeball with White Coilex Baffle
- 417P White Trim and Eyeball with Black Coilex Baffle
- 417PB Polished Brass Trim and Eyeball with Black Coilex Baffle



HOUSING / LAMP:
H6451C: 75W R30, 65W BR30
DIMENSIONS: OD: 8" [203mm]

1417 Low Voltage Eyeball with Baffle 30° Tilt

- 1417W White Trim with White Eyeball and White Baffle
- 1417BA White Trim with White Eyeball and Black Baffle



HOUSING / LAMP:
H7RT: 50W 12V MR16
H7T: 50W 12V MR16
H7TCP: 50W 12V MR16
DIMENSIONS: OD: 7-1/4" [184mm]
ACCESSORIES: Low Voltage Transformer Included

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Representative or visit www.cooperlighting.com for available options, accessories and ordering information.


7-INCH INCANDESCENT SLOPE CEILING HOUSING ICAT

FEATURES

- Got Nail™ bar hangers
- Pass-N-Thru™ tool-less shortening of bar hangers
- AIR-TITE™
- Quick Connect wiring connectors included in junction box
- Thermally protected
- Die-formed housing and plaster frame
- Socket aiming for ceilings from 2/12 to 12/12 pitch
- Slope indicator provides quick and consistent lamp settings

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

COMPLIANCES: UL/cUL Listed - Damp Location, UL/cUL Listed 1598 Luminaire, UL/cUL Listed for Feed Through, UL/cUL Listed for Insulation Contact, AIR-TITE™ Certified ASTM E283



H745ICAT

ORDERING INFORMATION: ORDER HOUSING AND TRIMS SEPARATELY^A

SAMPLE NUMBER: H745ICAT - 457W

Housing	Trims
H745ICAT=7" Aperture, New Construction, Slope Ceiling, IC AIR-TITE™, 120V Line Voltage	<p>Baffles</p> <p>457 Baffle, 65W BR30, 75W R30, 75W PAR30, 90W PAR38, OD: 9-3/4" [248mm]</p> <p>457P=White Trim with Black Baffle</p> <p>457W=White Trim with White Baffle</p> <p>Reflectors</p> <p>457 Specular Reflector, 75W R30, 65W BR30, OD: 9-3/4" [248mm]</p> <p>457CG=White Trim with Champagne Gold Reflector</p> <p>457SC=White Trim with Clear Specular Reflector</p> <p>White Cone Reflector</p> <p>457 White Reflector, 65W BR30, 75W R30, 75W PAR30, 90W PAR38, OD: 9-3/4" [248mm]</p> <p>457PW=White Trim with White Reflector</p>


NOTES: Δ Not to be used in direct contact with spray foam insulation.

457 Slope Ceiling Baffle



457W White Trim with White Baffle

457P White Trim with Black Baffle



HOUSING / LAMP:

H745ICAT: 65W BR30, 75W R30, 75W PAR30, 90W PAR38
H745ICAT: 75W R30, 65W BR30


DIMENSIONS: OD: 9-3/4" [248mm]

457 Slope Ceiling Specular Reflector



457SC White Trim with Clear Specular Reflector

457CG White Trim with Champagne Gold Reflector



HOUSING / LAMP:

H745ICAT: 75W R30, 65W BR30

DIMENSIONS: OD: 9-3/4" [248mm]

457 Slope Ceiling White Reflector



457PW White Trim with White Reflector




HOUSING / LAMP:

H745ICAT: 65W BR30, 75W R30, 75W PAR30, 90W PAR38

DIMENSIONS: OD: 9-3/4" [248mm]

PITCH TO DEGREE CONVERSION



Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Representative or visit www.cooperlighting.com for available options, accessories and ordering information.

6-INCH INCANDESCENT SLOPE CEILING HOUSING ICAT




H6451C

FEATURES

- Got Nail™ bar hangers
- Pass-N-Thru™ tool-less shortening of bar hangers
- Slide-N-Side™ wire traps
- Quick Connect wiring connectors included in junction box
- AIR-TITE™
- Thermally protected
- Die-formed housing and plaster frame
- Socket aiming for ceilings from 2/12 to 12/12 pitch
- Slope indicator provides quick and consistent lamp settings

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

COMPLIANCES: UL/cUL Listed - Wet Location, UL/cUL Listed - Damp Location, UL/cUL Listed 1598 Luminaire, UL/cUL Listed for Feed Through, UL/cUL Listed for Insulation Contact, AIR-TITE™ Certified ASTM E283



ORDERING INFORMATION: ORDER HOUSING AND TRIMS SEPARATELY*

SAMPLE NUMBER: H6451C - 456W

Housing	Trims	Baffles
H6451C —6" Aperture, New Construction, Slope Ceiling, IC AIR-TITE™, 120V Line Voltage	Adjustables 1417 Low Voltage Eyeball with Baffle - 30° Tilt, 50W 12V MR16, OD: 7-1/4" [184mm] 1417BA —White Trim with White Eyeball and Black Baffle (Low Voltage Transformer Included) 1417W —White Trim with White Eyeball and White Baffle (Low Voltage Transformer Included) 417 Coilex® Baffle Eyeball - 30° Tilt, 75W R30, 65W BR30, OD: 8" [203mm] 417P —White Trim and Eyeball with Black Coilex® Baffle 417PB —Polished Brass Trim and Eyeball with Black Coilex® Baffle 417W —White Trim and Eyeball with White Coilex® Baffle 78 Eyeball - 30° Tilt, 65W BR30, 75W R30, 75W PAR30L, OD: 8" [203mm] 78B —Satin Brass Trim with Satin Brass Eyeball 78P —White Trim with White Eyeball 78PAT —White Trim with White Eyeball - AIR-TITE™ Trim 78PB —Polished Brass Trim with Polished Brass Eyeball 78SN —Satin Nickel Trim with Satin Nickel Eyeball 78TBZ —Tuscan Bronze Trim with Tuscan Bronze Eyeball	Baffles 456 Baffle, 456P: 60W BR30, 50W PAR30L, OD: 7-1/4" [184mm] 456P —White Trim with Black Baffle 456 Baffle, 456W: 50W PAR30L, 65W BR30, and 75W PAR30L with H1999 Socket Extender, OD: 7-1/4" [184mm] 456W —White Trim with White Baffle Lenses and Diffusers 170 Albalite Lens with Reflector, 60W A19, OD: 8" [203mm] 170P —White Trim with Frosted Albalite Glass Lens 170PS —White Trim with Frosted Albalite Glass Lens, Wet Location Listed and AIR-TITE™
	Reflectors 455 Specular Reflector, 65W BR30, 75W R30, 75W PAR30L, OD: 7-1/4" [184mm] 455H —White Trim with Haze Reflector 455SC —White Trim with Clear Specular Reflector 455SCG —White Trim with Champagne Gold Reflector	

NOTES: Δ Not to be used in direct contact with spray foam insulation. Δ UL/cUL Listed for Wet Location with select trims.

455 Slope Ceiling Specular Reflector

- 455SSC White Trim with Clear Specular Reflector
- 455H White Trim with Haze Reflector
- 455CG White Trim with Champagne Gold Reflector

HOUSING / LAMP:
H6451C: 65W BR30, 75W R30, 75W PAR30L
DIMENSIONS: OD: 7-1/4" [184mm]

456 Slope Ceiling Baffle

- 456W White Trim with White Baffle
- 456P White Trim with Black Baffle

HOUSING / LAMP:
H6451C: 456P: 60W BR30, 50W PAR30L
H6451C: 456W: 50W PAR30L, 65W BR30, 75W PAR30L with H1999 Socket Extender
DIMENSIONS: OD: 7-1/4" [184mm]

78 Eyeball 30° Tilt

- 78P White Trim with White Eyeball
- 78PAT White Trim with White Eyeball - AIR-TITE™ Trim
- 78SN Satin Nickel Trim with Satin Nickel Eyeball
- 78TBZ Tuscan Bronze Trim with Tuscan Bronze Eyeball
- 78B Satin Brass Trim with Satin Brass Eyeball
- 78PB Polished Brass Trim with Polished Brass Eyeball

HOUSING / LAMP:
H6451C: 65W BR30, 75W R30, 75W PAR30L
DIMENSIONS: Height: 4-1/8" [105mm]; Aperture: 3-15/16" [100mm]; OD: 8" [203mm]

170 Albalite Glass Lens with Reflector

- 170P White Trim with Frosted Albalite Glass Lens
- 170PS White Trim with Frosted Albalite Glass Lens, Wet Location, AIR-TITE™

HOUSING / LAMP:
H6451C: 60W A19
DIMENSIONS: Height: 4" [101mm]; OD: 8" [203mm]

417 Coilex® Baffle Eyeball 30° Tilt

- 417W White Trim and Eyeball with White Coilex Baffle
- 417P White Trim and Eyeball with Black Coilex Baffle
- 417PB Polished Brass Trim and Eyeball with Black Coilex Baffle

HOUSING / LAMP:
H6451C: 75W R30, 65W BR30
DIMENSIONS: OD: 8" [203mm]

1417 Low Voltage Eyeball with Baffle 30° Tilt

- 1417W White Trim with White Eyeball and White Baffle
- 1417BA White Trim with White Eyeball and Black Baffle

HOUSING / LAMP:
H7RT: 50W 12V MR16
H7T: 50W 12V MR16
H7TCP: 50W 12V MR16
DIMENSIONS: OD: 7-1/4" [184mm]
ACCESSORIES: Low Voltage Transformer Included

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Representative or visit www.cooperlighting.com for available options, accessories and ordering information.


7-INCH INCANDESCENT SLOPE CEILING HOUSING ICAT

FEATURES

- Got Nail™ bar hangers
- Pass-N-Thru™ tool-less shortening of bar hangers
- AIR-TITE™
- Quick Connect wiring connectors included in junction box
- Thermally protected
- Die-formed housing and plaster frame
- Socket aiming for ceilings from 2/12 to 12/12 pitch
- Slope indicator provides quick and consistent lamp settings

Compliances may not apply to all product configurations. Please consult the product spec sheet for compliance details.

COMPLIANCES: UL/cUL Listed - Damp Location, UL/cUL Listed 1598 Luminaire, UL/cUL Listed for Feed Through, UL/cUL Listed for Insulation Contact, AIR-TITE™ Certified ASTM E283



H745ICAT

ORDERING INFORMATION: ORDER HOUSING AND TRIMS SEPARATELY^A

SAMPLE NUMBER: H745ICAT - 457W


Housing	Trims
H745ICAT=7" Aperture, New Construction, Slope Ceiling, IC AIR-TITE™, 120V Line Voltage	<p>Baffles</p> <p>457 Baffle, 65W BR30, 75W R30, 75W PAR30, 90W PAR38, OD: 9-3/4" [248mm] 457P=White Trim with Black Baffle 457W=White Trim with White Baffle</p> <p>Reflectors</p> <p>457 Specular Reflector, 75W R30, 65W BR30, OD: 9-3/4" [248mm] 457CG=White Trim with Champagne Gold Reflector 457SC=White Trim with Clear Specular Reflector</p> <p>White Cone Reflector</p> <p>457 White Reflector, 65W BR30, 75W R30, 75W PAR30, 90W PAR38, OD: 9-3/4" [248mm] 457PW=White Trim with White Reflector</p>

NOTES: Δ Not to be used in direct contact with spray foam insulation.

457 Slope Ceiling Baffle



457W White Trim with White Baffle
 457P White Trim with Black Baffle



HOUSING / LAMP:


H745ICAT: 65W BR30, 75W R30, 75W PAR30, 90W PAR38
 H745ICAT: 75W R30, 65W BR30

DIMENSIONS: OD: 9-3/4" [248mm]

457 Slope Ceiling Specular Reflector



457SC White Trim with Clear Specular Reflector
 457CG White Trim with Champagne Gold Reflector



HOUSING / LAMP:

H745ICAT: 75W R30, 65W BR30

DIMENSIONS: OD: 9-3/4" [248mm]

457 Slope Ceiling White Reflector



457PW White Trim with White Reflector




HOUSING / LAMP:

H745ICAT: 65W BR30, 75W R30, 75W PAR30, 90W PAR38

DIMENSIONS: OD: 9-3/4" [248mm]

PITCH TO DEGREE CONVERSION



Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Representative or visit www.cooperlighting.com for available options, accessories and ordering information.