



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



458 3-1/2" STL Emt Set/Screw Conn *Crouse-Hinds*

Catalog Number	458
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Emt Set Screw Type Connector, Emt, Straight, Non-Insulated, Steel, Two Tightening Screws, 3-1/2"
Weight per unit	1.9 (lbs/each)
Product Category	Steel Uninsulated Straight Set

Features

connection	Threaded
dimensions	5.8000 IN X 3.8000 IN X 6.4000 IN

Material, Color, and Finish

Finish	Zinc Plated
--------	-------------

Dimensions and Weight

Size	3-1/2 in
------	----------

Descriptions

Description	3-1/2" STL EMT SET/SCREW CONN
extra long description	MIDWEST 458 3 1/2 EMT RGD SS CONN
Features	Crouse-Hinds series EMT connectors and couplings are used to join EMT conduit to a box or enclosure, or to couple two ends of EMT conduit. Our EMT fittings are available in set screw type and compression type, in both insulated and non-insulated versions. They are available in steel and zinc die cast. Crouse-Hinds series EMT connectors and couplings are also available painted in seven different colors to better match architectural specifications and preferences.
Long Description	Eaton Crouse-Hinds series EMT set screw type connector, EMT, Straight, Non-insulated, Steel, Two tightening screws, 3-1/2"
Product Type	3 1/2 Emt RGD SS Conn

Manufacturer Information

Brand	Eaton
GTIN	00784564104588
UPC	784564104588

Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	Set screw type connector



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	4
Weight Per each	1.9

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL, cUL