

# shat-r-shield<sup>®</sup> INC.

## 46558

F32T8 ADV850/ALTO (PK X 30)



**Application:** Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

**Base:** Medium Bi-Pin (G13)

**Coating:** Copolymer

**Color Temperature:** 5000 K

**Diameter:** 1.00 IN

**Lamp Type:** Fluorescent

**Mean Design Lumens:** 3025

**Package Weight:** 15.40 L

**Shape:** T

**Type:** Straight Linear Fluorescent Lamp

**Wattage:** 32.0 W

**Average Life Hours:** 36000

**Bulb:** T8

**Color:** ADV850

**CRI:** 82

**Initial Lumens:** 3100

**Length:** 48.00 IN

**Package (LxWxH):** 49.80 IN x 6.50 IN x 7.90 IN

**Pack By:** 30

**Special Features:** Shatter-Resistant

**UPC:** 726585465583

ULEPH,ROHS,NSF Splash Zone



# 46558

F32T8 ADV850/ALTO (PK X 30)



**Application:** Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

**Base:** Medium Bi-Pin (G13)

**Coating:** Copolymer

**Color Temperature:** 5000 K

**Diameter:** 1.00 IN

**Lamp Type:** Fluorescent

**Mean Design Lumens:** 3025

**Package Weight:** 15.40 L

**Shape:** T

**Type:** Straight Linear Fluorescent Lamp

**Wattage:** 32.0 W

**Average Life Hours:** 36000

**Bulb:** T8

**Color:** ADV850

**CRI:** 82

**Initial Lumens:** 3100

**Length:** 48.00 IN

**Package (LxWxH):** 49.80 IN x 6.50 IN x 7.90 IN

**Pack By:** 30

**Special Features:** Shatter-Resistant

**UPC:** 726585465583

ULEPH,ROHS,NSF Splash Zone