



SERVICE PARTS LIST

BULLETIN NO.
54-40-0283

SPECIFY CATALOG NO. AND SERIAL NO. WHEN ORDERING PARTS		REVISED BULLETIN	DATE
TWO SPEED DEEP CUT BANDSAW		54-40-0282	Oct. '95
CATALOG NO. 6236	STARTING SERIAL NO. 769B	WIRING INSTRUCTION 58-01-1200	

EXAMPLE:
Component Parts (Small #) Are Included
When Ordering The Assembly (Large #).



FIG.	PART NO.	DESCRIPTION OF PART	NO. REQ.	FIG.	PART NO.	DESCRIPTION OF PART	NO. REQ.
1	22-64-3200	Cord Set	(1)	60	42-12-0070	Blade Pulley Axle	(2)
2	44-76-0120	Cord Protector	(1)	61	06-82-8864	10-24 x 1/2" Pan Hd. Sem T-25	(2)
3	31-17-0155	Cord Clamp	(1)	62	42-38-0041	Bumper	(1)
4	06-82-7270	8-16 x 5/8" Slt. Plastite T-20	(2)	63	06-82-5330	10-32 x 5/8" Pan Hd. Tapt. T-25	(2)
5	06-82-5292	1/4-20 x 7/8" Pan Hd. Taptite T-30	(6)	64	42-28-0205	Front Blade Guide Block	(1)
6	31-44-0507	Right Handle Half	(1)	65	42-28-0210	Rear Blade Guide Block	(1)
7	06-82-7270	8-16 x 7/8" Slt. Plastite T-20	(4)	66	02-25-0260	Cam Follower	(6)
8	31-44-0517	Left Handle Half	(1)	67	06-82-5574	10-24 x 7/8" Pan Hd. Tapt. T-25	(2)
9	23-16-1340	Insulator	(1)	68	06-82-8864	10-24 x 1/2" Pan Hd. Sem T-25	(1)
10	23-66-1855	Two Speed AC/DC Switch	(1)	69	43-54-0250	Blade Guard	(1)
11	06-82-7252	8-32 x 3/8" Pan Hd. Slt. Tapt. T-20	(1)	70	06-82-9264	10-24 x 1/2" Pan Hd. Tapt. Shld. T-25	(1)
12	28-62-0031	Blade Release Lever	(1)	71	48-39-0510	Bandsaw Blade	(1)
13	06-42-2200	Woodruff Key	(1)	★ 72	02-50-3235	Needle Bearing	(1)
14	45-88-7105	Wave Washer	(1)	73	14-73-0160	Blade Release Shaft Assembly	(1)
15	06-82-8828	8-32 x 5/16" Pan Hd. Tapt. T-20	(1)	74	45-36-0720	Retaining Plate Spacer	(4)
16	06-75-4675	3/8-16 x 1" Skt. Hd. Screw	(1)	75	44-52-0120	Blade Backing Pad	(1)
17	31-44-0330	Front Handle	(1)	76	28-41-0920	Front Pulley Guard	(1)
18	23-44-0220	Brush Cap	(2)	77	42-40-1010	Bronze Bushing	(1)
19	22-18-0670	Carbon Brush Assembly	(2)	78	44-66-0550	Pulley Guard Retaining Plate	(2)
20	22-22-1355	Brush Holder Assembly	(2)	79	06-82-3810	1/4-20 x 1-1/4" Flat Hd. Taptite T-27	(4)
21	06-82-5298	1/4-20 x 1" Pan Hd. Taptite T-30	(4)	80	40-50-0710	Blade Tension Spring	(2)
22	28-90-0200	Pulley Support	(1)	81	06-75-0255	1/4-20 x 4" Hex Hd. Screw	(2)
23	28-50-6380	Motor Housing	(1)	82	06-57-5000	1/4-20 Lock Nut	(2)
★ 24	02-04-0913	Ball Bearing	(1)	83	42-18-0190	Blade Tension Bar	(2)
25	31-55-0145	Coil Shield	(1)	84	06-82-5298	1/4-20 x 1" Pan Hd. Taptite T-30	(2)
26	23-16-0427	Field Insulator	(1)	85	06-82-3024	1/4-20 x 1/2" Fil. Hd. Taptite T-30	(3)
27	18-50-0110	120 Volt Field	(1)	86	22-84-0770	Fan	(1)
28	06-82-7410	8-16 x 1-7/8" Pan Hd. Plastite T-20	(2)				
29	31-05-0170	Fan Baffle	(1)				
30	16-50-0100	120 Volt Armature	(1)				
31	02-04-1050	Ball Bearing	(1)				
32	06-65-1155	3/16 x 5/8" Groove Pin	(1)				
33	28-28-1699	Diaphragm	(1)				
34	02-04-1020	Ball Bearing	(1)				
35	32-40-1680	Intermediate Gear	(1)				
36	06-42-1200	Woodruff Key	(1)				
37	36-18-0050	Worm Shaft	(1)				
38	02-04-1030	Ball Bearing	(1)				
39	28-14-2110	Gear Case	(1)				
40	06-82-3060	1/4-20 x 1-5/16" Pan Hd. Taptite T-30	(4)				
41	06-85-0200	Nameplate Screw	(2)				
42	12-99-0250	Nameplate Blank	(1)				
43	06-82-5394	5/16-18 x 13/16" Pan Hd. T-40	(2)				
44	02-04-1210	Ball Bearing	(1)				
45	32-90-0110	Worm Gear	(1)				
46	06-42-2200	Woodruff Key	(1)				
47	36-66-0525	Worm Gear Shaft	(1)				
48	02-04-2700	Ball Bearing	(1)				
★ 49	14-46-1175	Chain/Sprocket Kit	(1)				
50	06-82-8842	8-32 x 3/8" Pan Hd. Tapt. Sem T-20	(2)				
★ 51	-----	Roller Chain	(1)				
52	45-69-0010	Blade Pulley Tire	(2)				
53	45-88-7165	Pulley Hub Washer	(4)				
54	34-60-1400	Snap Ring	(2)				
55	28-20-1220	Blade Pulley Cover	(2)				
56	06-82-3060	1/4-20 x 1-5/16" Fil. Hd. Tapt. T-30	(3)				
57	28-95-0120	Blade Pulley	(2)				
58	42-40-0580	Sleeve Bearing	(4)				
★ 59	-----	Sprocket	(1)				

FIG. NOTES

34,35,
36,37,38 Assemble and install in Gear Case before 44 thru 48.

43 Apply Type 242 Blue Loctite. Torque to 75-115 in./lbs.

11,61, 63,67 Apply Type 242 Blue Loctite.

66 Torque to 20-25 in./lbs.

83 Dimension between outside edges of blade tension bars 3-11/16" ± 1/16".

FIG. LUBRICATION

39 3 oz. Type "G" Grease, No. 49-08-4140.
1.5 oz. in each of two locations. (See Illustration).

MILWAUKEE ELECTRIC TOOL CORPORATION
13135 W. LISBON RD., BROOKFIELD, WI 53005

