



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48404070 5-3/8" Metal/Stainless Cutting Circular Saw Blade

Milwaukee Electric Tool

Catalog Number	48404070
Manufacturer	Milwaukee Electric Tool
Description	Milwaukee Metal Circular Saw Blades Were Specifically Designed to Exceed The Expectations Of Contractors For Blade Life, Cut Quality, and Speed In The Most Demanding Metal Cutting Applications – Without A Lubricant. A Hand-Tensioned, Hardened Alloy Steel Body Extends Blade Life and Delivers The Highest Quality Cuts Available. Carbide Tipped Teeth With Alternate Top Bevel Grind Shear Through Metal Leaving Burr-Free, Cool-to-Touch Cuts. Designed For Use With The M18™ Cordless 5-3/8 In. Metal Saw, These Blade
Weight per unit	0.4200 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Blade Diameter	5 3/8
idea granular category code	1157

Dimensions and Weight

Size	5-3/8
------	-------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	5-3/8" METAL/STAINLESS CUTTING CIRCULAR SAW BLADE
extra long description	MILW 48-40-4070 5-3/8 in. Circular
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	Milwaukee metal circular saw blades were specifically designed to exceed the expectations of contractors for blade life, cut quality, and speed in the most demanding metal cutting applications – without a lubricant. A hand-tensioned, hardened alloy steel body extends blade life and delivers the highest quality cuts available. Carbide tipped teeth with alternate top bevel grind shear through metal leaving burr-free, cool-to-touch cuts. Designed for use with the M18™ cordless 5-3/8 in. metal saw, these blade
Product Type	5-3/8 In. Circular Saw Blade
Short Description	5-3/8 in. Circular Saw Blade
Special Features	Dry - no lubricant required, saving time and money with less mess; Cool - no extreme heat buildup preserves blade life and allows handling the work piece immediately; Clean - no burrs eliminates secondary operations saving time and money; Lasts up to 25x longer than abrasive blades; A hand-tensioned, hardened alloy steel body extends blade life and delivers the highest quality cuts available; Carbide tipped teeth with Alternate Top Bevel grind shear through metal leaving burr-free, cool-to-touch cuts; Thin

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242233786
Manufacturers Part Number	48-40-4070
UPC	045242233786

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	Circular Saw Blade



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	80
Weight Per each	0.42

Uses, Certifications, and Standards

Application	Metal
-------------	-------