

# Eaton 4867AN-BOX

Catalog Number: 4867AN-BOX

Eaton Arrow Hart straight blade plug , #18-12 AWG, 15A, Angled Commercial, 125V, Back wire, Yellow, Brass, Vinyl, 5-15P, Two-pole, three-wire, grounding, Screw, 0.25-0.66", Vinyl, ED Box

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Arrow Hart straight blade plug	4867AN-BOX
<b>UPC</b>	<b>Product Length/Depth</b>
032664536823	5.5 in
<b>Product Height</b>	<b>Product Width</b>
1.4 in	4.5 in
<b>Product Weight</b>	<b>Warranty</b>
0.1 lb	Refer to warranty document.
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	UL
	NOM
	Federal Specification Classification 6221 02

## Product specifications

### Device type

Plug

### Color

Yellow

### Face/body material

Vinyl

### Wiring method

Back wire

### Material

Vinyl

### Allowable wire size

#18-12 AWG

### Amperage Rating

15A

### Number Of Poles

Two-pole

### Contact material

Brass

### Type

Angled plug

### Device grade

Commercial specification grade

### NEMA configuration

5-15P

### Style type

Angled body

### Design type

Straight blade

### Connection type

Screw

### Number of wires

3

### Receptacle type

Two-pole, three-wire, grounding

### Cord range

## Resources

### Catalogs

[Arrow Hart Buyers Guide Section B](#)

### Multimedia

[Commercial and residential straight blade vinyl receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - 4867AN-BOX](#)

0.25-0.66" in diameter

Voltage rating

125V

Application

Commercial

Torque rating

14 lbf-inch

Packaging type

ED Box



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)