



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

48892716 5/32" Thunderbolt Black Oxide Drill Bit

Milwaukee Electric Tool

Catalog Number	48892716
Manufacturer	Milwaukee Electric Tool
Description	Milwaukee® Thunderbolt® Black Oxide Jobber Length Drill Bits Are Designed For Extreme Durability and Long Life. The Thunderbolt® Web Features A Thicker Core Than A Standard Drill Bit, Which Provides Ultimate Strength and Protects Against Side-Load Breakage. A Specially Designed Parabolic Flute Form Clears Chips and Debris Fast to Keep The Bit Cool. A Precision Start, 135 Split Point Tip Starts On Contact to Keep The Bit From Walking For Fast Accurate Holes. Excellent For Drilling On Curved Surfaces, Requir
Weight per unit	0.0250 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Drill Diameter	0.156
Flute Length	4.0
package quantity	1
Shank Diameter	0.25

Material, Color, and Finish

Finish	Black Oxide
--------	-------------

Dimensions and Weight

Length	6.0
--------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	5/32" THUNDERBOLT BLACK OXIDE DRILL BIT
extra long description	MILW 48-89-2716 5/32" Thunderbolt B
Features	5/32 in. Thunderbolt® Black Oxide Drill Bit
Long Description	Milwaukee® Thunderbolt® Black Oxide Jobber length drill bits are designed for extreme durability and long life. The Thunderbolt® web features a thicker core than a standard drill bit, which provides ultimate strength and protects against side-load breakage. A specially designed parabolic flute form clears chips and debris fast to keep the bit cool. A precision start, 135 Split Point tip starts on contact to keep the bit from walking for fast accurate holes. Excellent for drilling on curved surfaces, requir
Product Type	5/32" Thunderbolt Black Oxide
Special Features	Thunderbolt Web, Provides Longer Life And Faster Driller Times; Parabolic Flute, Clears Chips Faster; 135 DEG Degree Split Point, Precision Start No Walking; Point Type: Split Point; Flute Type: Parabolic; Drill Point: 135 DEG

Manufacturer Information

Brand	Milwaukee®
GTIN	04524216683124
Manufacturers Part Number	48-89-2716
series	Milwaukee® Thunderbolt® Black Oxide
UPC	045242166831

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
----------------------	-----------------------------

Packaging

Carton	1
Weight	0.025
Weight Per each	0.025

Uses, Certifications, and Standards

Application	For Portable Drills
-------------	---------------------