



## THREADED BRIDLE RING, 2" DIA, #14 SCREW, WOOD

### CATALOG NUMBER

**4BRT32WS**



### CERTIFICATIONS



### FEATURES

Combine bridle rings with other nVent CADDY fasteners to support cables from flange, purlin, drop wire, t-grid, etc.

### PRODUCT ATTRIBUTES

Material: Steel

Finish: Electrogalvanized

Diameter: 2"

Screw Diameter: 14"

Screw Type: Wood

Screw Length: 3/4"

Ultimate Static Load: 50lb

### ADDITIONAL PRODUCT DETAILS

Bridle Rings not recommended for high performance cables. See nVent CADDY Cat HP J-Hook System.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**



## THREADED BRIDLE RING, 2" DIA, #14 SCREW, WOOD

### CATALOG NUMBER

**4BRT32WS**



### CERTIFICATIONS



### FEATURES

Combine bridle rings with other nVent CADDY fasteners to support cables from flange, purlin, drop wire, t-grid, etc.

### PRODUCT ATTRIBUTES

Material: Steel

Finish: Electrogalvanized

Diameter: 2"

Screw Diameter: 14"

Screw Type: Wood

Screw Length: 3/4"

Ultimate Static Load: 50lb

### ADDITIONAL PRODUCT DETAILS

Bridle Rings not recommended for high performance cables. See nVent CADDY Cat HP J-Hook System.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**