



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 4DNW224ZN BLTF Nut & Washer

*Cooper B-Line/Cable Tray*

Catalog Number	4DNW224ZN
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series 4DIMENSION Strut Channel Nuts, Installs With Quarter Turn, Steel, Dove-Tail Slide-In Nut, Dove-Tail Combo Nut Washer, Electro-Plated Zinc, 400 LBS Pull Out Strength, 300 LBS Slip Strength, 3/8"-16 Thread Size
Weight per unit	0.1530 (lbs/each)
Product Category	Channel & Strut Fittings

### Material, Color, and Finish

Finish	Zinc Plated
--------	-------------

### Dimensions and Weight

Height	0.461 IN
Size	1.575 IN X 1.575 IN X 0.461 IN
Width	1.575 IN

### Descriptions

Description	BLTF NUT & WASHER
extra long description	B-LINE 4DNW224ZN 4D DOVETAIL COMBO
Features	The unique design of the 4Dimension strut channel nuts can be used on multiple sides of the 4Dimension strut channel, allowing for numerous designs and applications. The 4Dimension wire wing nut and the slide-In nuts can also be used with traditional strut.
Long Description	Eaton B-Line series 4Dimension strut Channel nuts, Installs with quarter turn, Steel, Dove-tail slide-in nut, Dove-tail combo nut washer, Electro-plated zinc, 400 lbs pull out strength, 300 lbs slip strength, 3/8"-16 thread size
Product Type	4D Dovetail Combo Nut Washer, 1/4"-20 Thread

### Manufacturer Information

Brand	Eaton
GTIN	00799038583189
Manufacturers Part Number	4DNW224ZN
UPC	799038583189

### Taxonomies, Classifications, and Categories

Category Description	MISC FITTINGS
Type	Strut channel nuts



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	100
Weight Per each	0.153

## Uses, Certifications, and Standards

standard	Not Applicable
----------	----------------