



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



51892 HBL 1G WP CVR, (3)1/2HUBS BRNZ

Hubbell--Raco

| | |
|------------------|--|
| Catalog Number | 51892 |
| Manufacturer | Hubbell--Raco |
| Description | 1G WP Cluster Cover (3) 1/2 In. Outlets Bronze |
| Weight per unit | 0.2500 (lbs/each) |
| Product Category | Bar Hangers & Outlet Box Accy. |

Features

| | |
|-----------------|--------|
| Packaging Type | Shrink |
| pallet quantity | 3000 |

Material, Color, and Finish

| | |
|--------|-------------|
| Color | Bronze |
| Finish | Powder Coat |

Dimensions and Weight

| | |
|----------|---------|
| Height | 4.594 |
| Hub Size | 0.5 |
| Length | 2.84375 |
| Width | 2.844 |

Descriptions

| | |
|------------------------|--|
| Construction | Metallic |
| Description | HBL 1G WP CVR,(3)1/2HUBS BRNZ |
| extra long description | RACO 5189-2 1G WP CLUSTER CVR (3) 1 |
| Long Description | 1G WP CLUSTER COVER (3) 1/2 IN. OUTLETS BRONZE |
| Product Type | Weatherproof Covers |
| Special Features | and multi-lingual instructions included;device mount; installation hardware;gasket;Three .5 in outlets;weatherproof protection |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | BELL |
| GTIN | 00050169518922 |
| Manufacturers Part Number | 5189-2 |
| UPC | 050169518922 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | WEATHERPROOF BOXES & COVERS |
| Type | COVER |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|------------------|------|
| Carton | 1 |
| Package | 20 |
| Standard Package | 20 |
| Weight Per each | 0.25 |

Uses, Certifications, and Standards

| | |
|-------------|------------|
| Application | Electrical |
| standard | UL 514A |